




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		B	REVISED PER ECO-14-011808	11AUG2014	AP	SB

D

C


B

A



P.C. BOARD MOUNTING DIMENSIONS

- 1 MOLDED PARTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED.COLOR: BLACK.
SHELLS & BRACKETS: CARBON STEEL
CONTACTS: BRASS
- 2 SHELLS: .000200 MIN TIN OVER .000100 MIN COPPER.
BRACKETS: .000200 MIN TIN OVER .000050 MIN COPPER.
CONTACTS: SEE TABLE
- 3 GOLD PLATED FOR LENGTH OF .150 MIN FROM MATING END, GOLD FLASH IN MATED AREA, .000100 MIN TIN ON OPPOSITE END, BOTH OVER .000050 MIN NICKEL.
- 4 GOLD PLATING FOR A LENGTH OF .150 MIN FROM MATING END, .000030 MIN GOLD IN MATED AREA, .000100 MIN TIN ON OPPOSITE END, BOTH OVER .000050 MIN NICKEL.
-OR-
GOLD FLASH OVER PALLADIUM NICKEL PLATED FOR A LENGTH OF .150 MIN FROM MATING END, .000030 MIN PALLADIUM NICKEL IN MATED AREA, .000100 MIN TIN ON OPPOSITE END, BOTH OVER .000050 MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



5	OBSOLETE	4	5745352-4
		3	-5745352=1
		CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. HENNY 8-24-05	TE TE Connectivity			
DIMENSIONS: INCHES		CHK S. BOLASH 8-24-05				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 8-24-05	NAME			
0 PLC ± -		PRODUCT SPEC	PLUG ASSEMBLY, SIZE 2, 15 POSITION, RIGHT ANGLE, .545 SERIES, .025 SQ. POSTS, AMPLITE HDP			
1 PLC ± -		108-40025	SIZE			
2 PLC ± -		114-40013	CAGE CODE			
3 PLC ± .005		WEIGHT	DRAWING NO			
4 PLC ± -		-	RESTRICTED TO			
ANGLES ± 2°		CUSTOMER DRAWING	SCALE			
FINISH		4:1	SHEET			
1		1 of 1	REV			
2		B				