


Circuit Diagram

技术特性

1. 规格 Rating: 2A 250V AC;4A 125V AC
2. 接触电阻 Contact R: 50 mΩMax
3. 绝缘电阻 Insulation R: DC 500V 1000MΩ Min
4. 耐压 Dielectric strength: AC 1500V,1 Minute
5. 操作温度 Operating temperature:-20℃~+65℃
6. 电气寿命 Electrical life:10,000 Cycles

Specification

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
		JAMECO NO. 76241		GOLDSUN NO. TS-1307	
DRAWN: Colin Hung		Description Toggle Switch Full Single Pole Single Throw (On-Off) Solder 125VDC @ 4 Amp 1/2 Inch Mounting			Rev. 1
VERIFY PEOPLE:		UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: