


GP Batteries

Data Sheet



Model No.: GP27A

Type	: Alkaline High Voltage Battery			
Chemical System	: Zinc / Manganese Dioxide			
Nominal Voltage	: 12V			
Nominal Dimension	: Ø 7.7 X 28.0mm			
Terminal	: Nickel plated flat contacts - protruded red (+); recessed black (-)			
Jacket	: Metal jacket			
Internal Connection	: Pressure			
Applications	: Remote controller			
Average Weight	: 4.4g			
Date Code	: Every battery will carry a numeric year code and an analogue month code changing bi-monthly. Year code 0 for 2000, 1 for 2001, etc.			
Shelf Life	: Not less than 95% of service life for 1 year storage at 20°C; Not less than 85% of service life for 3 year storage at 20°C			
Insulation Resistance	: 5 MΩ min.			
Close Circuit Voltage	: 10.5V (min.) (load resistor 1.6 kΩ at 20°C for 0.1 to 2 seconds)			
Current Drain	: Under 5mA pulse, 0.5mA continuous			
Nominal Capacity (to 6.0V at 20°C)	: 20 mAh (at 20 kΩ load)			
Average Service Life (to 6.0V at 20°C)	: 38 hrs (at 20 kΩ load)			
Cross Reference	:			
GP	Duracell	Eveready	Varta	Bronica
27A	--	--	--	B1

Normal Rate Discharge



High Rate Discharge



* The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GP27A](#)