




Sensor cables

M12 one end without connector shielded A-coded



Ordering data

Male, straight	
PUR halogen-free	1.5 m
Male, angled	
PUR halogen-free	1.5 m
Female, straight	
PUR halogen-free	1.5 m
Female, angled	
PUR halogen-free	1.5 m
Note	

3-pole

Type	Order No.
SAIL-M12G-3S1.5Q	1906470150
SAIL-M12W-3S1.5Q	1906500150
SAIL-M12BG-3S1.5Q	1867410150
SAIL-M12BW-3S1.5Q	1906950150
Other versions on request	

4-pole

Type	Order No.
SAIL-M12G-4S1.5Q	1906480150
SAIL-M12W-4S1.5Q	1059650150
SAIL-M12BG-4S1.5Q	1812540150
SAIL-M12BW-4S1.5Q	1808970150
Other versions on request	

5-pole

Type	Order No.
SAIL-M12G-5S1.5Q	1926690150
SAIL-M12W-5S1.5Q	1906520150
SAIL-M12BG-5S1.5Q	9456140150
SAIL-M12BW-5S1.5Q	1906540150
Other versions on request	

Standard cable lengths

All cables listed under the ordering data have a length of 1.5 metres. The last four ordering digits must be changed when ordering other standard cable lengths.	1.5 m	xxxxxx0150
	3.0 m	xxxxxx0300
	5.0 m	xxxxxx0500
	10.0 m	xxxxxx1000

Technical data

Rated current	4 A
Protection class	IP 67
Core cross-section	0.34 mm ²
Contact surface	gold-plated
Temperature range of housing	-25...+85 °C
Rated voltage	250 V (3- and 4-pole) / 125 V (5-pole)
(acc. to VDE standard 0110 ISO group C)	

Chapter W includes additional technical specifications for the cable

Dimensioned drawing

