



Wiha Insulated Nut Drivers



322 Nut Driver, With Wiha-SoftFinish® Handle Insulation

According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E, up to 1000 Volt. Individually Tested.

Blade CVM steel, hardened. Insulation molded directly onto blade. Deep drawn 1" socket. Wiha-SoftFinish® handle, multi-component.

Item No.	mm	mm	mm	Inch	lbs.	pkg.
322 06	4.0	125	236	9.3	.15	10
322 09	5.0	125	236	9.3	.16	10
322 12	5.5	125	236	9.3	.16	10
322 15	6.0	125	236	9.3	.16	10
322 18	7.0	125	243	9.6	.25	10
322 21	8.0	125	243	9.6	.25	10
322 24	9.0	125	243	9.6	.25	10
322 27	10.0	125	243	9.6	.27	10
322 30	11.0	125	243	9.6	.37	10
322 33	12.0	125	243	9.6	.38	10
322 36	13.0	125	243	9.6	.39	10



322 Nut Driver, With Wiha-SoftFinish® Handle. Inch sizes.

Item No.	Inch	Inch	mm	Inch	lbs.	pkg.
322 55	5/32	5.0	236	9.3	.15	10
322 58	3/16	5.0	236	9.3	.15	10
322 61	7/32	5.0	236	9.3	.16	10
322 64	1/4	5.0	243	9.5	.24	10
322 67	5/16	5.0	243	9.5	.25	10
322 68	11/32	5.0	242	9.5	.26	10
322 70	3/8	5.0	243	9.5	.26	10
322 73	7/16	5.0	243	9.5	.36	10
322 76	1/2	5.0	243	9.5	.39	10
322 78	9/16	5.0	243	9.5	.39	10
322 80	5/8	5.0	243	9.5	.41	10

Item No.	Inch	Inch	Inch	Inch	lbs.
322 96	322 55	5/32	5.0	322 70	3/8 5.0
	322 58	3/16	5.0	322 73	7/16 5.0
	322 61	7/32	5.0	322 76	1/2 5.0
	322 64	1/4	5.0	322 78	9/16 5.0
	322 67	5/16	5.0	322 80	5/8 5.0
	322 68	11/32	5.0		

1000Volt [SHOP](#)

Warning!

Insulated tools are not intended for use on live or energized circuits. Always disconnect and de-energize all equipment & circuits. **NEVER!** work on live or energized circuits or equipment.

Use & Care Guide For Insulated Tools:

Store tools to minimize risk of damage to insulation
Inspect insulation prior to each use of any insulated tool
If you doubt the integrity of the insulation destroy the tool or have it retested
Use insulated tools where the ambient temperature is between -20 to +70° C
Have a qualified safety technician inspect and re-certify tools annually for safe use



Item No.	mm	mm	mm	mm	lbs.
322 91	322 15	6.0	125	322 24	9.0 125
	322 18	7.0	125	322 27	10.0 125
	322 21	8.0	125		



Item No.	mm	mm	mm	mm	lbs.
322 93	322 09	5.0	125	322 21	8.0 125
	322 12	5.5	125	322 27	10.0 125
	322 15	6.0	125	322 36	13.0 125
	322 18	7.0	125		



Item No.	Inch	Inch	Inch	Inch	lbs.
322 92	322 61	7/32	5.0	322 70	3/8 5.0
	322 64	1/4	5.0	322 76	1/2 5.0
	322 67	5/16	5.0		



Item No.	Inch	Inch	Inch	Inch	lbs.
322 94	322 58	3/16	5.0	322 70	3/8 5.0
	322 61	7/32	5.0	322 73	7/16 5.0
	322 64	1/4	5.0	322 76	1/2 5.0
	322 67	5/16	5.0		