

Waterproof Miniature Illuminated Rocker



Features

- **Waterproof:** IP65
- **Single Pole**
- **.187" Quick Connect Terminals**



S110






Table 1. Mounting Hole

Panel Thickness	X
.030 (.750) - .059 (1.50)	.764 (19.40)
.059 (1.50) - .098 (2.50)	.780 (19.80)



Specifications

Current Rating: 16A 125VAC 1/3 HP, 10A 250VAC 1/2 HP
Lamp Voltage: 110V Neon (AC) & 12V LED (DC)
Insulation Resistance: 100 Megohms (min.) at 500VDC
Dielectric Strength: 1000V RMS (min.)
Temperature Rating: +32° to +185°F (0° to +85°C)
Electrical Life: 10,000 cycles
Mechanical Life: 50,000 cycles at full load
Terminal Type: .187" Tab Q.C.
Mounting Hole: See Table 1

NTE Type No.	Circuitry	Action	Actuator				Diag No.
			Material	Color	Neon	LED	
54-200W	SPST	ON	PC	Red	-	AC	S110
54-201W	SPST	ON	PC	Red	-	DC	S110
54-202W*	SPDT	ON	PC	Black	-	N/A	S110
54-203W	SPST	ON	PC	Green	-	AC	S110
54-204W	SPST	ON	PC	Green	-	DC	S110

* Designates Non-Illuminated Type

Waterproof Round Illuminated Rocker





Features

- **Waterproof:** IP65
- **Single Pole**
- **.187" Quick Connect Terminals**



S117



Specifications

Current Rating: 16A 125VAC, 10A 250VAC
Lamp Voltage: 110V Neon (AC) & 12V LED (DC)
Insulation Resistance: 100 Megohms (min.) at 500VDC
Dielectric Strength: 1500V RMS (min.)
Temperature Rating: +32° to +185°F (0° to +85°C)
Electrical Life: 10,000 cycles
Mechanical Life: 50,000 cycles at full load
Terminal Type: .187" Tab Q.C.
Mounting Hole: .795 (20.2)

NTE Type No.	Circuitry	Action	Actuator				Diag No.
			Material	Color	Neon	LED	
54-503W*	SPST	ON	Nylon	Black	-	N/A	S117
54-526W	SPST	ON	Nylon	Green	-	AC	S117
54-527W	SPST	ON	Nylon	Red	-	DC	S117
54-529W	SPST	ON	Nylon	Green	-	DC	S117
54-531W	SPST	ON	Nylon	Red	-	AC	S117

* Designates Non-Illuminated Type