


Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 50mA / 12VDC
- Contact Resistance: 100m Ω Max.
- Insulation Resistance: 100M Ω Min.
- Dielectric Strength: 250VAC for 1 Minute

Mechanical Specifications:

- Operating Life: 50,000 Cycles
- Operating Temperature: -25°C to +70°C

Soldering Process:

- Temperature: 260 $\pm$ 5°C 5 $\pm$ 1 sec.

Tactile Switches
TS6211T2602AC, TS6211T3202AC

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-TS6211T3202AC](#) [101-TS6211T2602AC](#)