

42" Diagonal Plasma TV

Model number: TH-42PD60U

[Print this](#) | [Share this](#)

Product no longer available for purchase.

42" Diagonal Plasma TV with Built-In
ATSC/QAM/NTSC Tuners and HDMI Interface

Online Order Assistance

- [Track your order](#)
- [Print your invoice](#)
- [Read our shipping FAQs](#)
- [Register your product](#)

Accessories

- [Find accessories for your product](#)

Contact Us

- [Live Chat](#)
- [Phone](#)
- [Email](#)
- [Mail](#)
- [International Support](#)

Operating Manuals	Help & Tutorials	FAQs	Tech Specifications	Warranty & Care Plans	Drivers & Downloads
VIDEO:					
Screen Size				42	
Contrast Ratio				Up to 10,000:1	
Compatible Signal Formats				480p (EDTV)	
Aspect Ratio				16:9 (Widescreen)	
Displayable Colors				Maximum of 29 Billion	
Shades of Gradation				3,072	
Pixel Pitch (H x V)				1.08 x 1.08 mm	
Panel Type				9th Generation Plasma Panel	
Aspect Control for TV/AV Modes				4:3, Zoom, Full, Just, H-Fill	
Native Resolution (Number of Pixels)				852 x 480	
Progressive Scan				Yes	
Video Noise Reduction				Yes	
Digital Comb Filter				Motion Adaptive 3D-Y/C	
Color Purity Optimizer (3D Color Management)				Yes	
Sub-Pixel Controller				Yes	
Motion Pattern Noise Reduction				Yes	
AUDIO:					
Speakers				2 (20W, 8 ohms, 80Hz - 17kHz, 10% THD)	
Surround Sound				Yes	
BBE® VIVA HD3D Sound				No	
INPUT/OUTPUT:					
Tuners				NTSC (Standard analog broadcasts) ATSC/QAM (SDTV and HDTV broadcasts)	
Photo Viewer				No	
SD Card Slot				No	
CableCARD Ready				No	
HDMI-HDCP Interface				Yes	
Analog Audio Input (for HDMI)				1 rear	
Composite Video Input				2 rear	
S-Video Input				2 rear	
Audio Input (for Video)				2 rear	
PC Input (RGB-VGA)				No	
Audio Input (for PC)				No	
Component Video Input [Y, PB(CB), PR(CR)]				2 rear	
Audio Input (for Component Video)				2 rear	
Composite Video Output				1 rear	
Audio Output				1 rear	
Digital Audio Out				1 (optical)	
CONVENIENCE:					
EZ Sync™ HDAVI Control				Yes, via HDMI interface	
TV Guide® On-Screen Program Guide				No	
Video Picture Memory				Yes	
On-Screen Display Languages				English/Spanish/French	
Picture-In-Picture				No	
P-I-P Scalable Size				No	
V-Chip Program Lockout				Yes	
Built-In Closed Caption Decoder				Yes	
Timers - Sleep/On/Off				Sleep (Off only)	
Video Input Labeling				Yes	
GENERAL:					
Power Supply				AC 120 V, 60 Hz	
Power Consumption				345 W	
Operating Temperature				32°F - 104°F	
Operating Humidity				20% - 80% (Non condensation)	
Pedestal Stand				Included	
Remote Control				Included	
Dimensions (H x W x D) w/Stand				30.1" x 42.1" x 12.6"	
Weight (lbs.) w/Stand				68.3 lbs	
Dimensions (H x W x D)				27.6" x 42" x 3.8"	
Weight				63.9 lbs.	