



FCIconnect.com

Copyright FCI

SHELL	A±0.38	B±0.12	C±0.10	D +0.25 0	E±0.07	G	TIN LEAD P/N	TIN LEAD P/N	LEAD FREE P/N	LEAD FREE P/N
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15 0	D09P81C4GL00	D09P81C6GL00	D09P81C4GL00LF	D09P81C6GL00LF
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15 0	D15P81C4GL00	D15P81C6GL00	D15P81C4GL00LF	D15P81C6GL00LF
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25 0	D25P81C4GL00	D25P81C6GL00	D25P81C4GL00LF	D25P81C6GL00LF
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25 0	D37P81C4GL00	D37P81C6GL00	D37P81C4GL00LF	D37P81C6GL00LF
Detail of grounding strip							Gold flash	0.76 µ gold	Gold flash	0.76 µ gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ✓	ISO 406 ISO 1101		D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
G	ELX-I-18050	MP	2014/06/23	angles	linear				
				0°±2°					
				dr	PESSON	1996/12/06	MALE CONNECTOR DELTA-D EUROPE RIGHT ANGLED PRESS FIT		
				engr	MITHUN PAUL	2014/06/23			
				chr	ALIAS BABU	2014/06/23			
				appd	BIJU K PAUL	2014/06/23			
sheet index	revision sheet	G	1				dwg no	sheet 1 of 1	size
							C01-8646-0521		A3
							type Product Customer Drawing		