


LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
FT	8		N1	REVISED PER ECO-13-009250	27JUN13




- 1

0.76µm [.000030] MIN GOLD OVER 1.27µm [.000050] MIN NICKEL.
- 2

1.27µm [.000050] MIN TIN OVER NICKEL FLASH.
- 3

ASSEMBLY MATES WITH PIN ASSEMBLY 202422.

OBSOLETE	2	202417-4
	1	202417-1
SOCKET BODY FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.CARBO 18 DEC 97		 TE Connectivity				
		CHK R.STONE 09 JAN 98						
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME CONTACT ASSEMBLY, SOCKET, WIRE SIZE 12-14, TYPE I				
		APVD G.STEINHAUER 30 JAN 98						
		PRODUCT SPEC —						
		APPLICATION SPEC —						
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
SEE CALLOUTS		SEE CALLOUTS		WEIGHT —	A2	00779	C=202417	—
CUSTOMER DRAWING				SCALE	10:1	SHEET	1 of 1	REV N1