

HC-B 10-TFL-45/O1PG16G

Order No.: 1673517

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1673517>

Sleeve housing, for single locking latch, height 45 mm, without screw connection, 1x Pg16, straight cable entry

Commercial data

GTIN (EAN)	 4 017918 152321
sales group	D002
Pack	10 pcs.
Customs tariff	85389099

Product notes

WEEE/RoHS-compliant since:
03/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Note	For contact inserts HC-B10, BB18, DD42, M, K8/24
Design	B10
Height	45 mm
Width	43 mm
Length	73 mm

Housing type	Sleeve housings
Locking type	for single locking latch
Cable exit	Straight
Type of the screw connection	1x Pg16
Pg screw connection	None
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;