


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	MAX. COMBINED BUNDLE DIA. D1 + D2 in (mm)	A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs/100 pcs. (g)
PLB4H	3.6 (91)	.075 (1.91)	.300 (7.62)	.974 (24.74)	.322 (8.18)	.490 (12.45)	14.4 (366)	120 (534)	HEAVY	1.45 (660)

NOTES:

1. SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
2. PRODUCT IS RoHS COMPLIANT.

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS						
										W10001CU/05-SS_27268.PRT						
										PANDUIT CORP. TINLEY PARK, ILLINOIS						
										BOW - TY CABLE TIE PLB SERIES						
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .0005 (XXX) ± .020 (.51) (.XX) ± .02 (.5) ANGLES ± .0005		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.				
										DRAWN BY JABO	MAT'L: NYLON 6.6		SCALE NONE			
5	12/17/09	JABO	BOBK	REMOVED PART FROM DRAWING		27268	5	BOBK		DATE 7/12/00			DRAWING NO. SS-27268		DWG A SIZE	
REV	DATE	BY	CHK	DESCRIPTION		ECN	R	CUST	SUP	CHK'D BOBK						