


.7mm DC Power Plug

171-3118-EX



.7mm DC Power Plug



Dimensions: mm (In)

SPECIFICATIONS

| | |
|-----------------------------|---------------------|
| Rating: | 2A/3.15VDC |
| Dielectric Strength: | 500VAC for 1 Minute |
| Insulation Resistance: | 100MΩ min. @ 500VDC |
| Contacts: | Nickel Plated Brass |
| Insulator: | POM |
| Body: | Polypropylene |
| RoHS Compliant by Exemption | |

Date Last Revised: 12-9-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300909

171-3118-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-3118-EX](#) [171-3118-E](#)