

Starfix® ferrules and crimping tools



0376 50



0376 60



0376 61



0376 62



0376 63



0376 87



0376 64



0376 66



0376 67



0376 68



0376 43



0376 09 + refill 0376 43



Adjustable cross section



0376 39



0376 06



0376 92

Technical information p. 149

Pack	Cat. Nos.	Ferrules with insulating flange			
		Provide an equipotential link for all the strands of a flexible conductor Active part in tinned electrolytic copper Conform to NF C 63-023			
		Single ferrules (in strips) Supplied in strips to prevent loss of ferrules			
		For cables cross section (mm²)	Colour	Strips	Ferrules
500	0376 50	0-25	turquoise	10	50
500	0376 60	0-34	green	10	50
480	0376 61	0-5	white	12	40
480	0376 62	0-75	blue	12	40
1000	0376 63	1-0	red	25	40
1000	0376 64	1-5	black	25	40
1000	0376 66	2-5	grey	25	40
250	0376 67	4-0	orange	10	25
250	0376 68	6-0	green	10	25
		Individual ferrules - single			
100	0376 69	10	brown		
100	0376 70	16	white		
50	0376 71	25	black		
		Individual ferrules - double			
100	0376 87	2 x 0-75	blue		
100	0376 88	2 x 1-0	red		
100	0376 89	2 x 1-5	black		
100	0376 90	2 x 2-5	grey		
		Large capacity refills Large capacity for less frequent applicator reloading Translucent packaging For direct mounting on crimping tool Cat. No. 0376 09			
		Cross section (mm²)	Colour	Number of ferrules per strip	
3000	0376 41	0-5	White	300	
3000	0376 42	0-75	Blue	300	
3000	0376 43	1-0	Red	300	
3000	0376 44	1-5	Black	300	
2500	0376 45	2-5	Grey	250	

Colours according to NF C 63-023 standard


Cross sections in mm² :	0-5	0-75	1	1-5	2-5	4	6

Pack	Cat. Nos.	Crimping tools for ferrules in strips	
		Cut and carry out 4-point crimping of ferrules from 0-25 to 6 mm² in one operation Recommended for spring connections Dedicated applicator for each crimping tool for dispensing strips For right and left-handed usage 4 point crimping for Cat. Nos. 0376 08/09 3 point crimping for Cat. No. 0376 10	
1	0376 08	For ferrules with 0-25 and 0-34 mm² cross sections Supplied with empty applicator fitted	
1	0376 09	For ferrules with 0-5 to 2-5 mm² cross sections Fitted with an adjustment wheel Supplied with empty applicator fitted	
1	0376 10	For ferrules with 4 and 6 mm² cross sections Fitted with an adjustment wheel Supplied complete with empty applicator	
1	0376 39	Transport case for on-site use Assorted kit, comprising : - 1 Starfix crimping tool, Cat. No. 0376 09 with empty applicator fitted - 120 x 0-5 mm² ferrules - 120 x 0-75 mm² ferrules - 240 x 1-0 mm² ferrules - 320 x 1-5 mm² ferrules - 200 x 2-5 mm² ferrules	
1	0376 97	Multi-purpose crimping tool for 0-5 to 2-5 mm² cross sections Tool cuts, strips, twists, crimps Supplied complete with 5 empty applicators	
		Crimping tool for single and double ferrules	
		Starfix crimping tool for 0-25 to 6 mm² cross sections For 4-point crimping of ferrules from 0-25 to 6 mm² Recommended for spring connections Crimping tool with disengageable control system, crimping at end For right and left-handed usage	
1	0376 06		
1	0376 92	Transport case for on-site use Assorted kit. Supplied with : - 1 tool with crimping operation control system for individual ferrules 10 to 50 mm² - 30 individual ferrules 10 mm² - 20 individual ferrules 16 mm² - 15 individual ferrules 25 mm² - 10 individual ferrules 35 mm² - 10 individual ferrules 50 mm²	


applicators for Starfix® crimping tools



0376 47



Example of single/double ferrules fitted on cables



Example of use with Viking 3 terminals

Technical information **opposite**

Pack Cat. Nos. **Starfix applicators**

For Starfix crimping tools		For Starfix crimping tools	
For dispensing strips of ferrules in Starfix crimping tools Cat. Nos. 0376 08/09/10/97		For dispensing strips of ferrules in Starfix crimping tools Cat. Nos. 0376 08/09/10/97	
Pack	Cat. Nos.	For ferrules cross section (mm²)	Colour
10	0376 46	0.25 and 0.34	yellow
10	0376 47	0.5 to 2.5	red
10	0376 48	4 and 6	orange


Starfix® ferrules, crimping tools and applicators

■ Correspondance table

Cross section (mm²)			
Ferrule	Single ferrule	Large capacity ferrule - refills	Starfix applicator
0-5	0376 61	0376 41	0376 47
0-75	0376 62	0376 42	0376 47
1-0	0376 63	0376 43	0376 47
1-5	0376 64	0376 44	0376 47
2-5	0376 66	0376 45	0376 47


■ Dimensions (mm)

Single ferrules



Cat. Nos.	Cross section (mm²)	A	B	C	D
0376 50	0.25	8	14.5	1.1	3
0376 60	0.34	8	14.5	1.1	3
0376 61	0.5	8	14.5	1.5	3.4
0376 62	0.75	8	14.5	1.5	3.4
0376 63	1.0	8	14.5	1.7	3.6
0376 64	1.5	8	14.5	2	4.1
0376 66	2.5	8	14.5	2.6	4.8
0376 67	4	12	21	3.2	5.7
0376 68	6	12	23	3.9	7.2
0376 69	10	12	21	4.9	8.1
0376 70	16	18	29	6.3	9.8
0376 71	25	18	31	7.9	12

Double ferrules



Cat. Nos.	Cross section (mm²)	A	B	C	D	E
0376 87	2 x 0.75	8	15	2.1	6	3.3
0376 88	2 x 1.0	8	15	2.35	6	4
0376 89	2 x 1.5	8	16	2.6	7.2	4.2
0376 90	2 x 2.5	10	18.5	3.3	8.4	4.8

■ Starfix crimping tool usage example



1 Fit the applicator



2 Adjust



The handle gives an excellent grip



3 Insert the cable



4 Crimp