



**Part Number: 68129-0511**
**2.50mm Pitch Board-to-Board Header, One-Piece, Right-Angle, 3.20/5.30mm Length PC Tail, 5 Circuits**


**Status:** **OBsolete**  
**Replacement:** Contact Molex  
**Series:** 68129  
**Category:** PCB Headers

*Series Image - Reference only*
**Product Environmental Compliance**
EU RoHS: Compliance Status Not Reviewed

China RoHS:
REACH SVHC: Not Reviewed

Low-Halogen Status: Not Reviewed

**Part Detail**
**General**

<b>Status</b>	<b>Obsolete</b>
Category	PCB Headers
Series	<b>68129</b>
Application	Signal, Wire-to-Board
Product Name	N/A

**Physical**

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Durability (mating cycles max)	30
Glow-Wire Compliant	No
Lock to Mating Part	None
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.20mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Polarized to Mating Part	No
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20°C to +85°C

**Electrical**
**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	1A
Voltage - Maximum	250V

**Material Info**
**Reference - Drawing Numbers**

Product Specification	PS-68129-001
Sales Drawing	SD-68129-001

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application**
**Tooling**
[Check our list of old tooling that used to be available for this part](#)