

Honeywell Sensing and Control

Search

**192-303KET-A01 Discrete Thermistors**

(Home : Products)

narrow your search

Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7016)
- Switches (9736)

Technology

- Control and Instrumentation (1063)
- Electromechanical (9297)
- Microstructure (2298)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

192 Series, Uni-Curve with bare leads and epoxy, 30,000 Ohm resistance, ± 1.0 °C [1.8 °F] tolerance, 25/85 BETA = 3943*Actual product appearance may vary.***Sales & Service****Distributor Inventory****Need Help?**

Click here to contact us

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)**Product Specifications**

| | |
|-----------------------|-------------------------------------|
| Availability | Global |
| Resistance | 30,000 Ohm |
| Tolerance | ± 1.0 °C [1.8 °F] |
| Accuracy | 0 °C to 70 °C [32 °F to 158 °F] |
| Beta | 3943 |
| Operating Temperature | -60 °C to 150 °C [-76 °F to 302 °F] |
| Diameter | 2,413 mm [0.095 in] |
| Termination Material | 32 Gauge tinned copper, alloy 180 |
| Lead Length | 38,1 mm [1.50 in] |
| Time Constant in Air | 15.0 s |
| Dissipation Constant | 0,75 m/W°C |
| Series Name | 192 |