


- Features
 - Surface Mount Packaging
 - Wide Frequency Range
 - Internal or external loading capacitance
- Specifications

Series SMRN




SERIES	SMRN-A	SMRN-B	SMRN-A1	SMRN-B1
FREQUENCY RANGE	16.000 ~ 48.000 MHz		3.580 ~ 48.000 MHz	
FREQUENCY TOLERANCE AT 25°C	±0.5 % MAX			
FREQUENCY STABILITY OVER -20°C TO +80°C	±0.3 % MAX	±0.3 % MAX	±0.5 % MAX	±0.5 % MAX
EQUIVALENT SERIES RESISTANCE (ESR)	100 OHMS MAX	100 OHMS MAX	100 OHMS MAX	100 OHMS MAX
CAPACITANCE	EXTERNAL	INTERNAL	EXTERNAL	INTERNAL
AGING AT 10 YEARS	±0.3 % MAX			

NOTE: CERTAIN FREQUENCIES MAY NOT BE AVAILABLE, CONSULT RALTRON FOR INFORMATION.

● Outline Drawings





LOWER HEIGHTS AVAILABLE





Series SMRN

Test Circuits



Carrier Tape Dimensions



Part Numbering System

Series	Frequency	Configuration	Tape and Reel
SMRN	in MHz	A B B1 A1	TR

Example: SMRN-20.000-A-TR
SMRN-3.58-B1-TR