


## 10 W 4000 K

---

Indoor LED batten luminaires



---

## Technical data

---

### Electrical data

Operating mode	Electronic control gear
Nominal wattage	10 W
Nominal voltage	220...240 V
Mains frequency	50/60 Hz

### Light technical data

Color temperature	4000 K
Beam angle	120 °
Light color as per EN 12464-1	Cool white
Color rendering index Ra	≥ 80

### Dimensions & weight

Length	600.0 mm
Width	25.0 mm
Height	44.0 mm

---

### Colors & materials

Body material	Aluminium
Product color	Silver
Cover material	PC

### Temperatures

Ambient temperature range	-20...+40 °C
---------------------------	--------------

### Capabilities

Type of installation	Surface-mounted
Dimmable	No
Type of connection	Cable with plug
Accessories	Power cable / Interconnection plug / Interconnection cable / Mounting clips

### Certificates & standards

Protection class	II
Type of protection	IP20

Product datasheet

Country specific categorizations

Order reference	72141
-----------------	-------

Country specific information

Product code	METEL-Code	SEG-No.	STK number	UK Org
4052899909304	-	-	4107830	-

## Product datasheet

---

### Logistical Data

---

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4052899909304	LUMCOM LED 10 W 4000 K	Folding carton box 1	53 mm x 52 mm x 596 mm	1.64 dm <sup>3</sup>	445.00 g
4052899909342	LUMCOM LED 10 W 4000 K	Shipping carton box 2	72 mm x 125 mm x 628 mm	5.65 dm <sup>3</sup>	1540.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

---

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.