






JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
SM0640G	6.0	.040	.048	0.60	5,000	C-2V
SM06200G	6.0	.200	.334	4.20	5,000	C-2R
SM1220G	12.0	.020	.032	0.40	5,000	C-2V
SM1250G	12.0	.050	.160	2.01	5,000	C-2V
SM12100G	12.0	.100	.255	3.21	5,000	C-2V
SM2420G	24.0	.020	.064	0.80	5,000	C-2F
SM2450G	24.0	.050	.279	3.51	5,000	C-2F
SM3020G	30.0	.020	.104	1.31	5,000	C-2F
SM3050G	30.0	.050	.319	4.00	5,000	C-2F
SM4840G	48.0	.040	.358	4.50	5,000	CC-2F
SM6020G	60.0	.020	.184	2.30	5,000	CC-2F



DIMENSIONS ARE
IN MILLIMETERS

TOLERANCE UNLESS
OTHERWISE SPECIFIED

1 PL +/- 0.2

2 PL +/- 0

ANGLE +/- 0

JKL

COMPONENTS CORPORATION

TITLE

T-2 TELEPHONE SLIDE BASE T6.8

DRAWN BY
L. WENGSTROM

APPV'D BY DATE
QC 10/9/01

SIZE
A

FSCM NO.
55335

DRAWING
NO.

SLIDE BASE T6.8

- CAD DRAWING -
MANUAL REVISIONS NOT PERMITTED

SCALE
NONE

RELEASED
DATE **8/16/00**

REVISION
DATE **10/9/01**

REV.
NO. **B**

SHEET
1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE
B	DELETE PART NO. SM2845G	10/9/01
A	ADD SM3050G & SM6020G	8/31/00
	RELEASED	8/16/00