



FEATURES:

- Convert a BNC Female receptacle into Minipincer® Test Clips

MATERIALS:

Conn: 1st End - Minipincer® Test Clips. Selectively gold plated Beryllium Copper contact.

Insulation: Nylon

Color: One Black and one Red

Cable: RG58C/U, 5.0 (.195) O.D.; Y-Mold insulation, PVC, Black

Conn: 2nd End – Crimp BNC Male – Brass body, tarnish resistant plated.

Center Contact: Brass, gold plated

Boot: PVC, Black

Marking: "POMONA 5423"

RATINGS:

Operating Temperature: +50° (+122°F) Max.

Operating Voltage: 300 VRMS Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 5423-C-XX

XX= Cable Length, Standard Length: 18" (457), 24" (610), 36" (914), 48" (1219), 60" (1542)

Ordering Example: 5423-C-60 indicates 60" in length.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5423-C-48](#) [5423-C-36](#) [5423-C-24](#)