



|                        |                 |
|------------------------|-----------------|
| <b>Catalog Number:</b> | <b>325</b>      |
| <b>Product ID:</b>     | 7TAA106020R0015 |
| <b>UPC Number:</b>     | 78621000325     |
| <b>Status:</b>         | A               |

Metal-Clad and Armored Cable Fitting, 90 Degree Bend, Trade Size 3/4 Inch, Knockout Size 3/4 Inch, Cable Range 0.906 to 1.093 Inch, Malleable Iron with Zinc Plating

- Throat is long enough to install in cast housing knockouts.
- To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

#### North American Specifications (UNSPSC)

|                  |  |
|------------------|--|
| UNSPSC           | 39121419 Flex connectors   |
| IGCC             | 4573 Flex connectors   |
| Brand Name       | T&B  |
| Type             | Armored Cable/Flexible Metal Conduit Fittings  |
| Special Features | The Angle Clip Gives Secure Mechanical Grip that Tightens Under Tension or Vibration |
| Application      | For Use with Armored Cable and Flexible Metal Conduit                                |
| Standard         | UL E23018, CSA 2884  |
| Size             | 3/4 Inch   |
| Conductor Range  | 0.906 to 1.093 Inch  |
| Material         | Steel  |
| Finish           | Electro Zinc Plated  |
| Color            | Metallic   |

#### European Specifications (ETIM)

|   |  |
|---|--|
| ETIM  | EC001180 Screw connection for protective metallic hose |
| Nominal size in inch                        | 3/4 inch   |
| Model                                       | 90°-elbow  |
| Revolving thread                            | N  |
| Construction type                           | External thread  |
| Connection type screw connection to housing | Other  |
| Material housing                            | Other  |
| Surface protection                          | Zinc coated  |
| Thread length                               | 19.05mm  |

#### Packaging

|                           |                 |
|---------------------------|-----------------|
| Inner Quantity            | 10              |
| Inner Dimensions (inches) | 6x4x4           |
| Outer Quantity            | 50              |
| Outer Dimensions (inches) | 21.6x5.2x7.1    |
| Weight Uom                | 28 lbs. per 100 |

#### Documents / Support Tools

|                                       |                      |
|---------------------------------------|----------------------|
| Technical Drawing / Data Sheet US     | Available on Website |
| Technical Drawing / Data Sheet Canada | Available on Website |

#### Header

|          |                      |
|----------|----------------------|
| 3D Model | Available on Website |
|----------|----------------------|

**For further technical assistance, please contact us...**

Memphis, TN 38120  
www.tnb.com

860 Ridge Lake Blvd.  
Memphis, TN 38120

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com