

8-Port NetDirector 1U Rackmount Console KVM Switch w/17" LCD

MODEL NUMBER: **B020-008-17**



Specifications

OVERVIEW	
# Of Users	1
Console	Yes
Port Control	Push Buttons, Hotkeys, OSD
Max CPU	8
PC/Server	PS/2
Shipping Weight	47.4 lbs.
Cat5 KVM Switch	No
IP Remote Access	No
Style	1U Rackmount Console
UPC ASSIGNMENT	
Unit Carton UPC#	037332125385
PHYSICAL	
Unit Dimensions (hwd / in.)	1.75 x 16.75 x 24
Unit Dimensions (hwd / cm)	4.45 x 42.55 x 60.96
Color	Black
LCD Monitor (in.)	17

LCD Monitor (cm)	43.18
ENVIRONMENTAL	
Relative Humidity	0% TO 80% RH
Operating Temperature	32 DEGREES TO 120 DEGREES F
BTUs	76.1 BTUs at 120V, 50Hz or 83.98 BTUs at 230V, 50Hz
CONNECTIONS	
Ports	8
Computer/Server Ports	(x8) HD15 (Female)
Local Console Ports - Port 1	HD15 (Female)
Local Console Ports - Port 2	(x2) MiniDIN6 (Female)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#):

[B020-008-17](#)