

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


82-26-6824

Status:

Active

Description:

1.27mm Pitch Round Conductor Flat Cable - 26 AWG (7 x 34) Stranded Tinned, 24 Circuits, Reel 30.48m Length



Series

image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR61126
UL	E61522

General

Product Family	Cable
Series	8863
Crimp Quality Equipment	Yes
Geographic Area	Asia
Product Name	Ribbon
UPC	800754996679

Physical

Cable Length	30.48m
Circuits (Loaded)	24
Insulation	PVC
Net Weight	2281.824/g
Packaging Type	Reel
Pitch - Termination Interface	1.27mm
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	26
Wire/Cable Type	(7x34) Stranded, Tinned

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	300V

Material Info

Old Part Number	8863-24-100B
-----------------	--------------

Reference - Drawing Numbers

Sales Drawing	SD-8863-001
---------------	-------------

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

8863Series

Use With

70121 MX-50™ Slimline Ribbon Cable.
90584 Picoflex® PF-50 IDT Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION