


REV.	DATE	ECR NO.	DESCRIPTION
A	01/07/04	XXXXXX	UPDATE DRAWING FORMAT
B	06/22/11	2186	ADD NOTE 1, 2, 3



1. IMPEDANCE: 75 OHMS
2. FREQUENCY RANGE: 0-1 GHz
3. MAX. PANEL THICKNESS: 4.5MM

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.				APPROVALS	DATE	<b>Amphenol Connex</b>	
5	HEX NUT	BRASS	NICKEL	1	DRAWN M.ZHANG		06/22/11
4	LOCK WASHER	BRASS	NICKEL	1	CHECKED		
3	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1	ISSUED		
2	INSULATOR	DELIN	NATURAL	1	SHEET 1 OF 1		
1	BODY	BRASS	NICKEL	1	CAD FILE		
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm $\pm$ 0.20mm 8 - 30mm $\pm$ 0.40mm 30 - 120mm $\pm$ 0.50mm				DO NOT SCALE DRAWING		PART DESCRIPTION <b>BNC FEMALE TO FEMALE BULKHEAD ISOLATED ADAPTOR - 75 OHM</b>	
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = $\pm$ 0.007" .315 - 1.180 = $\pm$ 0.015" 1.180 - 4.724 = $\pm$ 0.020"				C:/CONNEX/112440.DWG			
DESCRIPTION				MATERIAL		PART NO. <b>112440</b>	
FINISH				QTY		DWG. NO. 112440.DWG	
						REV. B SIZE A SCALE NA	