

6 rotatable outlets, direct plug-in, 1500 joule - Protect It! Surge Suppressor

MODEL NUMBER: **SWIVEL6**



Highlights

- 6 rotatable outlets
- Direct plug-in design
- 1500 joule rating
- Diagnostic LEDs
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for any desktop, network or home computing application requiring AC protection.

Package Includes

- SWIVEL6 Surge Suppressor
- Instruction manual with warranty information

Description

The SWIVEL6 offers reliable surge and line noise protection. Premium features include a compact, direct plug-in design for easy portability, six rotatable outlets for easier plug connection and removal and 1500 joules of surge absorption protection. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 6 rotatable outlets allow for easier plug connection and removal
- 1500 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 2 diagnostic LEDs alert user to protection and grounding status
- High-impact plastic housing (black) stands up to the most demanding environments
- Direct plug-in design converts two outlets into six by plugging into any wall outlet
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

General Info	
Product Group	SURGE PROTECTORS
OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency Compatibility	60 Hz



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Circuit Breaker (amps)	15
Outlet Quantity / Type	6 NEMA 5-15R
Number of Outlets	6
Outlet Orientation	Rotatable
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1500
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	330
UL1449 Let Through Rating	400, 500, 500
EMI / RFI Filtering	Up to 20 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	8.6 x 5.8 x 2.38
Shipping Dimensions (hwd / cm)	21.84 x 14.73 x 6.05
Shipping Weight (lbs.)	1.0
Shipping Weight (kg)	0.45
Unit Dimensions (hwd / in.)	6.25 x 4 x 2.25
Unit Dimensions (hwd / cm)	15.88 x 10.16 x 5.72



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (lbs.)	0.6
Unit Weight (kg)	0.27
Material of Construction	Plastic
Housing Color	Black
Receptacle Color	Black
Style	Direct Plug-in
Outlets Measurement (Center to Center)	29mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
cUL / CSA (Canada)	cUL
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.