

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT INVENTORY NUMBERING SYSTEM

HSTT4A 15 . 48 . 0

— PACKAGE QUANTITY: 5 = 5 pcs.
0 = 25 pcs.

— LENGTH: 48 = 48" (1219mm)

— EXPANDED INSIDE DIAMETER TUBING SIZE

— ADHESIVE LINED 4:1
THIN WALL HEAT SHRINK TUBING.

PANDUIT PART NO.	Min. exp. I.D. in / (mm)	Max. Rec. I.D. in / (mm)	NOMINAL REC WALL THICKNESS in / (mm)
HSTT4A15-_-_-	0.158 (4.0)	0.039 (1.0)	0.043 ±0.012 (1.10 ±0.30)
HSTT4A31-_-_-	0.315 (8.0)	0.079 (2.0)	0.043 ±0.012 (1.10 ±0.30)
HSTT4A47-_-_-	0.472 (12.0)	0.118 (3.0)	0.055 ±0.012 (1.40 ±0.30)
HSTT4A62-_-_-	0.630 (16.0)	0.158 (4.0)	0.070 ±0.012 (1.80 ±0.30)
HSTT4A94-_-_-	0.945 (24.0)	0.236 (6.0)	0.088 ±0.022 (2.25 ±0.55)
HSTT4A125-_-_-	1.26 (32.0)	0.315 (8.0)	0.100 ±0.022 (2.54 ±0.55)
HSTT4A200-_-_-	2.05 (52.0)	0.512 (13.0)	0.100 ±0.022 (2.54 ±0.55)

NOTES:

- SHRINK RATIO: 4:1
- SHRINK RATIOS ARE APPROXIMATIONS; PLEASE REFER TO TABLE 1 FOR THE EXACT MINIMUM EXPANDED AND MAXIMUM RECOVERED I.D.'S.
- MATERIAL: POLYOLEFIN WITH ADHESIVE
- COLOR: BLACK
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G03597HN_DC_GB0239NR/00A

PANDUIT

CORP. TINLEY PARK, ILLINOIS

FLEXIBLE ADHESIVE LINED
THIN WALL HEAT SHRINK
4:1 SHRINK (HSTT4A-_-_-)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
[.X] ±0.05 [1.3] [XXX] ±0.010 [0.25]
[.XX] ±0.02 [0.5] ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JADUKES

MAT'L:

SCALE NONE

DATE
8/26/08

SEE NOTES

DRAWING NO.

GB0239NR

DWG
SIZE
A

00A	8/26/08	JAD		INITIAL RELEASE	GB0239NR	00A			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	