

LOC	DIST	REVISIONS					
DF	DO	P	LTR	DESCRIPTION	DATE	DWN	APVD
			S	REV PER ECO-08-030008	22JAN2009	PK	RL




1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308.
2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .054 DIA.
3. METAL RETENTION CLIPS ARE INCLUDED IN INSERTS.
4. THIS RCPT. WILL ACCEPT SIZE 22 SOCKET CONTACT M39029/57-354 OR ANY TYCO HDD-22 SOCKET CONTACT. CONTACTS ORDERED SEPARATELY.

5 MFG'S PART NO. MARKED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS.

6 UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL.

7 FINISH: CADMIUM PER QQ-P-416.

8 FINISH: BRIGHT TIN PER ASTM-B-545 .000400-.000550 THK
OVER COPPER PER AMS2418 .000050 MIN THK.



	—	—	204508-5	—		STEEL, CLASS G	POLYPHENYLENE SULFIDE(PPS) PER MIL-M-24519, TYPE GST-40F COLOR: BLACK	204508-5
SUPSD BY 204508-1	—	—	—	—	—	STEEL, CLASS G	PHENOLIC COLOR: BLACK	204508-3
SUPSD BY 206505-4	—	—	—	—	—	BRASS	DIALLYL PATHALATE COLOR: BLUE	204508-2
	M24308/2-290F	M24308/2-15F	204520-2			STEEL, CLASS G	POLYPHENYLENE SULFIDE(PPS) PER MIL-M-24519, TYPE GST-40F COLOR: BLACK	204508-1
	MILITARY P/N ON PACKAGE	MILITARY P/N ON CONNECTOR	MFG'S P/N ON CONNECTOR	REMARKS	SHELL FINISH	SHELL MAT'L	INSERT MAT'L	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 01-DEC-87 DWG F.C.BALLEW 25-JAN-88 APP'D F.C.BALLEW 25-JAN-88		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLG ± . 1 PLG ± . 2 PLG ± . 3 PLG ± .005 4 PLG ± . ANGLES ± 0°30'		NAME AMPLITUDE RCPT FOR SOCKET CONTACTS HI-DENSITY D CONNECTOR SIZE 5 (78 POSN) SERIES 90	
MATERIAL SEE TABLE		FINISH SEE CALLOUTS		PRODUCT SPEC — APPLICATION SPEC — WEIGHT —	
				SIZE A1	
				CAGE CODE 00779	
				DRAWING NO 204508	
				RESTRICTED TO —	
				CUSTOMER DRAWING SCALE 4:1 SHEET 1 OF 1 REV S	