

Mounting Rails NS 35/7,5



Description	Type	Order No.	Pcs.	Pkt.
Mounting rail, acc. to EN 50 022: 1977 – 35 x 7.5 mm, yellow chromated, low profile, length: 2 m	unperforated	NS 35/7,5 UNPERFORATED	08 01 68 1	1
	perforated	NS 35/7,5 PERFORATED	08 01 73 3	1
Mounting rail, dimensions acc. to EN 50 022: 1977 – 35 x 7.5 mm, low profile, length: 2 m, material: copper	unperforated	NS 35/7,5-CU UNPERFORATED	08 01 76 2	1
Mounting rail, acc. to EN 50 022: 1977 – 35 x 7.5 mm length: 2 m, material: high-grade steel V2A	unperforated	NS 35/7,5-V2A UNPERFORATED	08 01 37 7	1
Cylindrical screw, for fixing the mounting rail, extra flat screw head, M 6 x 12.8, with allen wrench size 3	ZKS M 6 x 12 SW 2,5	08 07 02 5		100

Technical data

Material

steel, see description for divergence

Dimensional drawing

