

USA/English | [Select a country](#)
[Sign In/ Register](#)

Think Automation and beyond...

[HOME](#)
[PRODUCTS](#)
[SUPPORT](#)
[ABOUT US](#)
[NEWS](#)
[CONTACT](#)

HOME
 ▶ Industrial Components
 ▶ Switches & Pilot Devices
 ▶ HW Series
 ▶ HW4F-2F22QD-W-24V

Product Families

- ▶ Automation
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

HW4F-2F22QD-W-24V
 22mm Selector Switch Lighted



MSRP: ****

Add to Cart

Key Features

- Finger safe (IP20) screw terminals standard, other terminal styles available
- All E-Stops meet EN418 (IEC compliant, positive action)
- UL listed, CSA certified, TUV approved, and CE marked
- Super bright incandescent or LED illumination
- IP65 and NEMA type 1, 2, 3, 3R, 4, 4X, 5, 12, and 13
- 600V/10A contacts with a wide operating range from 5mA at 3V AC/DC to 10A at 120V AC



- Specifications
- Literature
- Downloads

Operation Type	Maintained
Product Type	Selector Switch Illuminated
Mounting Hole Size	Φ22mm
Shape	Round
Color	White
Normally Open Contacts	2
Normally Closed Contacts	2
Number of Positions	2
Illumination Voltage	24V AC 24V DC