


## Panel Cutout

## Illumination Options



## FEATURES:

- Up to 2 Pole and 2 Throw
- High Ratings with UL Approvals
- Full Illumination Options
- PVC Cap for Water Protection

## SPECIFICATIONS:

### RATING: RATING OPTION C:

- 15A 125VAC [UR, cUR]
- 10A 250VAC [UR, cUR]
- 1/3HP 125/250VAC [UR, cUR]

### RATING OPTION 3:

- 10A 125VAC [UR, cUR]

TEMPERATURE: -20°C to 105°C [UR, cUR]

ELECTRICAL LIFE: 10,000 Cycles

CONTACT RESISTANCE: 35mΩ Max. at 50VAC

INSULATION RESISTANCE: 100MΩ Min. at 500VAC

DIELECTRIC STRENGTH: 1,500VAC for 1 Minute

## MATERIALS:

BODY: Polyamide 6/6, UL94 V-2

ACTUATOR: Polyamide 6/6, UL94 V-2

Polycarbonate, UL94 V-2

CONTACTS: Silver Alloy

TERMINALS: Silver Plated Copper

RRA1631129



RRA16C112S / ACC-P04

| Series | Terminal      | Function                                                                                                       | Rating                           | Body Color                                                  | Actuator Color                                                                                                        | Marking Color                                 | Marking Type                                                                                                                                         | Lens Style | Lens Color                                                 | Lamp Voltage                                         |
|--------|---------------|----------------------------------------------------------------------------------------------------------------|----------------------------------|-------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|-----------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|------------|------------------------------------------------------------|------------------------------------------------------|
| RRA    | 1 - 4.8mm Tab | 1 Pole:<br>1 - Off-On<br>3 - On-On<br>5 - On-Off-On<br><br>2 Pole:<br>2 - Off-On<br>6 - On-On<br>6 - On-Off-On | 3 - 10A 125VAC<br>C - 15A 125VAC | 1 - Black<br>2 - White<br>3 - Almond<br>4 - Grey<br>9 - Red | 0 - Full Illum.<br>1 - Black<br>2 - White<br>3 - Almond<br>4 - Grey<br>5 - Orange<br>7 - Blue<br>8 - Green<br>9 - Red | 0 - None<br>1 - Black<br>2 - White<br>8 - Red | 0 - None<br>1 - I/O Vert.<br>2 - ON/OFF/ON Vert.<br>3 - ON/OFF Vert.<br>4 - ON/OFF Horiz.<br>9 - I/O/II Horiz.<br>S - I/O/II Vert.<br>R - I/O Horiz. | 1 - Full   | 0 - Clear<br>1 - Red<br>2 - Amber<br>3 - Green<br>4 - Blue | 3 - 6V<br>4 - 12V<br>5 - 24V<br>6 - 125V<br>7 - 250V |

Custom Colors and Markings Available Upon Request

For Illuminated Switches Only

## EXAMPLE PART NUMBERS:

RRA1G31100 2P On-On  
Black Body/Actuator, No Marking

RRA1631100 2P On-Off-On  
Black Body/Actuator, I/No Marking



E-SWITCH®

www.e-switch.com

800.867.2717