




RF Series
Rivet Feet



Specifications:

- Rivet Material: Nylon 6
- Foot Material: TPE
- Color: Black



Features:

- Feet are supplied with incorporated push rivets to quickly and easily install into pre-drilled holes
- Can be removed by pushing the plunger back thru from the opposite side

Item No.	Panel Thickness		Hole Dia		d		D		H		Pack Qty.	Bulk Pack Qty.
	In	mm	In	mm	In	mm	In	mm	In	mm		
RF100B	0.031 - 0.071	0.8 - 1.8	0.122 - 0.126	3.1 - 3.2	0.531	13.5	0.559	14.2	0.217	5.5	1	500
RF105B	0.071 - 0.110	1.8 - 2.8	0.122 - 0.126	3.1 - 3.2	0.531	13.5	0.559	14.2	0.217	5.5	1	500
RF110B	0.013 - 0.071	0.8 - 1.8	0.161 - 0.165	4.1 - 4.2	0.790	20.0	0.827	21.0	0.165	4.2	1	500
RF115B	0.071 - 0.110	1.8 - 2.8	0.161 - 0.165	4.1 - 4.2	0.790	20.0	0.827	21.0	0.165	4.2	1	500
RF120B	0.114 - 0.146	2.9 - 3.7	0.161 - 0.165	4.1 - 4.2	0.790	20.0	0.827	21.0	0.165	4.2	1	500
RF125B	0.150 - 0.189	3.8 - 4.8	0.161 - 0.165	4.1 - 4.2	0.790	20.0	0.827	21.0	0.165	4.2	1	500
RF130B	Max 0.020	(max 0.8)	0.161 - 0.165	4.1 - 4.2	0.551	14.0	0.591	15.0	0.236	6.0	1	500
RF135B	0.024 - 0.039	0.6 - 1.0	0.161 - 0.165	4.1 - 4.2	0.551	14.0	0.591	15.0	0.236	6.0	1	500
RF140B	0.039 - 0.079	1.0 - 2.0	0.161 - 0.165	4.1 - 4.2	0.551	14.0	0.591	15.0	0.236	6.0	1	500
RF145B	0.079 - 0.118	2.0 - 3.1	0.161 - 0.165	4.1 - 4.2	0.551	14.0	0.591	15.0	0.236	6.0	1	500
RF150B	0.031 - 0.047	0.8 - 1.2	0.200 - 0.205	5.1 - 5.2	0.551	14.0	0.591	15.0	0.236	6.0	1	500
RF155B	0.051 - 0.091	1.3 - 2.3	0.200 - 0.205	5.1 - 5.2	0.551	14.0	0.591	15.0	0.236	6.0	1	500
RF160B	0.031 - 0.071	0.8 - 1.8	0.161 - 0.165	4.1 - 4.2	0.790	20.0	0.827	21.0	0.236	6.0	1	500
RF165B	0.075 - 0.110	1.9 - 2.8	0.161 - 0.165	4.1 - 4.2	0.790	20.0	0.827	21.0	0.236	6.0	1	500
RF170B	0.114 - 0.157	2.9 - 4.0	0.161 - 0.165	4.1 - 4.2	0.790	20.0	0.827	21.0	0.236	6.0	1	500
RF175B	Max 0.020	(max 0.8)	0.161 - 0.165	4.1 - 4.2	0.790	20.0	0.827	21.0	0.315	8.0	1	500
RF180B	0.039 - 0.079	1.0 - 2.0	0.161 - 0.165	4.1 - 4.2	0.790	20.0	0.827	21.0	0.315	8.0	1	500
RF185B	0.083 - 0.118	2.1 - 3.0	0.161 - 0.165	4.1 - 4.2	0.790	20.0	0.827	21.0	0.315	8.0	1	500
RF190B	0.024 - 0.039	0.6 - 1.0	0.161 - 0.165	4.1 - 4.2	0.551	14.0	0.591	15.0	0.354	9.0	1	500
RF195B	0.039 - 0.079	1.0 - 2.0	0.161 - 0.165	4.1 - 4.2	0.551	14.0	0.591	15.0	0.354	9.0	1	500
RF200B	0.079 - 0.118	2.0 - 3.1	0.161 - 0.165	4.1 - 4.2	0.551	14.0	0.591	15.0	0.354	9.0	1	500
RF205B	0.031 - 0.047	0.8 - 1.2	0.200 - 0.205	5.1 - 5.2	0.551	14.0	0.591	15.0	0.354	9.0	1	500
RF210B	0.059-0.087	1.5 - 2.2	0.200 - 0.205	5.1 - 5.2	0.551	14.0	0.591	15.0	0.354	9.0	1	500
RF215B	0.020 - 0.047	0.5 - 1.2	0.142 - 0.146	3.6 - 3.7	0.394	10.0	0.425	10.8	0.157	4.0	1	500
RF220B	0.047 - 0.079	1.2 - 2.0	0.142 - 0.146	3.6 - 3.7	0.394	10.0	0.425	10.8	0.157	4.0	1	500
RF225B	0.059 - 0.087	1.5 - 2.2	0.142 - 0.146	3.6 - 3.7	0.394	10.0	0.425	10.8	0.157	4.0	1	500
RF230B	0.098 - 0.126	2.5 - 3.2	0.142 - 0.146	3.6 - 3.7	0.394	10.0	0.425	10.8	0.157	4.0	1	500
RF235B	0.138 - 0.177	3.5 - 4.5	0.142 - 0.146	3.6 - 3.7	0.394	10.0	0.425	10.8	0.157	4.0	1	500


FBR
Foot, Fir-Tree Mount

- Rigid nylon fir-tree mount provides exceptional retention strength
- Rubber foot provides skid resistance and vibration control
- Material: Rivet: UL94 V-2 Nylon 6/6
- Foot: TPE
- Color: Black



Item No.	Hole Ø	Min. Panel Thickness	Pack Qty.	Bulk Pack Qty.
FBR-1	.268 (6.8)	.394 (10)	1	1,000

BPM
Pull Mount Bumper



- Pulled from the inside of chassis
- High temperature silicone helps to cushion and prevent skidding
- Material: Silicone Rubber, 65 Shore A

Item No.	Hole Ø	Panel Thickness	"A"	Color	Pack Qty.	Bulk Pack Qty.
BPM-1	.24 - .25 (6 - 6.35)	.059 (1.5)	.118 (3)	Grey	1	1,000
BPM-2	.24 - .25 (6 - 6.35)	.059 (1.5)	.165 (4.2)	Black	1	1,000
BPM-3	.24 - .25 (6 - 6.35)	.059 (1.5)	.196 (5)	Black	1	1,000