





LOC	DIST	P	F	ZONE	LTR	REVISIONS		
						DESCRIPTION	DATE	APPD
AD	14				F	REDRAWN PER AD-5103 & ADDED -3 PER 91-5283-001	3/91	MB
					G	REVISED PER AD6120	4/28/92	MB
					H	REVISED PER AD6367	4/28/92	MB
					J	REACTIVATED -3 PER 91-5283-001	12/21/92	MB
					K	REVISED PER 0010-0072-96	5/16/96	RB MB
					L	REVISED PER 0010-0825-96	12/3/96	RB MB




- 1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC. COLOR: BROWN.
- 2 CONTACT: PHOSPHOR BRONZE.
- 3 CONTACT FINISH: .000100 MIN NICKEL ALL OVER. .000030 MIN GOLD OVER NICKEL IN CONTACT AREA. .000100 MIN TIN-LEAD OVER NICKEL ON SOLDER TAILS.
- 4 DISTANCE FROM CONTACT POINT TO BOTTOM OF CARD SLOT.
- 5 AMP PART NUMBER, DATE CODE AND CSA LOGO MARKED IN APPROXIMATE AREA SHOWN.

SECTION L-L
SCALE 8:1



RECOMMENDED CONNECTOR MOUNTING HOLE PATTERN
(CONNECTOR SIDE SHOWN)



RECOMMENDED MATING BOARD EDGE CONFIGURATION

OBSOLETE-	.125	650092-3
	.14	650092-2
	.10	650092-1
	W	PART NUMBER

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± .01 3 PLC DEC ± .005 ANGLES ± 2°		DR 3/21/91 K.L.CLOUSER/UTA		AMP AMP Incorporated Harrisburg, PA 17105-3608		
MATERIAL		CHK 7-22-91 M BOWERS				
HOUSING: 1 CONTACT: 2		APPD 7-22-91 M BOWERS		NAME CONNECTOR ASSEMBLY, 91 DUAL POSITION, .050 SERIES, STANDARD EDGE		
		APPD 7-23-91 M THUMMA				
		PRODUCT SPEC 108-14034				
FINISH		APPLICATION SPEC 114-26012		SIZE D	CAGE CODE 00779	DRAWING NO 650092
CONTACT: 3		WEIGHT _		SCALE 4:1		SHEET 1 OF 1