







PRODUCT NUMBER
85853-XXX OR 85853-XXXX
85853-XXYLF OR 85853-XXYYLF



mat'l code				tolerances unless otherwise specified				CUSTOMER				FCI			
ltr	ecn no.	dr	date	linear	0.X ±0.3	0.XX ±0.13	0.XXX ±0.051	projection	MM	scale	2:1	product family	METRAL	code	213
CW	V06-0569	DCH	2006-06-13	linear	0.XX ±0.13	0.XXX ±0.051	0° ±2°	projection	MM	scale	2:1	product family	METRAL	code	213
CX	DG09-0256	TER	2009-08-19	angles	0° ±2°	0° ±2°	0° ±2°	projection	MM	scale	2:1	product family	METRAL	code	213
-	-	-	-	angles	0° ±2°	0° ±2°	0° ±2°	projection	MM	scale	2:1	product family	METRAL	code	213
CS	V04-0408	TAB	04/27/04	dr	T.BRUNGARD	11/19/99	11/19/99	projection	MM	scale	2:1	product family	METRAL	code	213
CT	V04-0353	DAI	05/02/04	enr	M.STRAWER	11/19/99	11/19/99	projection	MM	scale	2:1	product family	METRAL	code	213
CU	V04-0559	HTB	06/01/04	chr	M.STRAWER	11/19/99	11/19/99	projection	MM	scale	2:1	product family	METRAL	code	213
CV	V04-1100	DAI	01/25/05	appd	M.STRAWER	02/29/00	02/29/00	projection	MM	scale	2:1	product family	METRAL	code	213
sheet index	revision	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX
sheet	sheet	1	2	3	4	5	6	7	8	9	10	11	12	13	14



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
9	5.00	17.00
10	5.75	17.00
19	8.00	4.30
20	8.00	13.60
21	8.00	17.00
25	5.75	15.60
33	7.25	12.90
36	5.75	14.40
49	5.75	15.10
64	5.75	14.90
67	7.25	16.30

mat'l code				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3		COPY		
CX					0.XX ±0.13		projection 	title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
					.XXX ±.051				
				angles	0° ±2°				
		dr	T.BRUNGARD	11/19/99	 MM	product family			METRAL
		enrg	M.STRAWSE	11/19/99		size	dwg no	85853	213
		chr	M.STRAWSE	11/19/99		scale			
		appd	M.STRAWSE	02/29/00	1:1		2		
sheet	revision								
index	sheet								

cage code 22526

Pro/E

PDM: Rev: CX

STATUS: Released

Printed: Jan 17, 2011



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X01 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X02 SEE NOTE 10 LEAD FREE OPTION	E	3	3	19	3	3	19	3	3	19	3
	D	3	19	3	3	19	3	3	19	3	3
	C	19	3	3	19	3	3	19	3	3	19
	B	3	3	19	3	3	19	3	3	19	3
	A	3	19	3	3	19	3	3	19	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X03 SEE NOTE 10 LEAD FREE OPTION	E	19	3	19	3	19	3	19	3	19	3
	D	3	19	3	19	3	19	3	19	3	3
	C	19	3	19	3	19	3	19	3	19	3
	B	3	19	3	19	3	19	3	19	3	3
	A	19	3	19	3	19	3	19	3	19	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X04 SEE NOTE 10 LEAD FREE OPTION	E	10	10	10	10	10	10	10	10	10	10
	D	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X05 SEE NOTE 10 LEAD FREE OPTION	E	7	6	5	5	5	5	5	5	5	5
	D	7	6	5	5	5	5	5	5	5	5
	C	7	6	5	5	5	5	5	5	5	5
	B	7	6	5	5	5	5	5	5	5	5
	A	7	6	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X06 SEE NOTE 10 LEAD FREE OPTION	E	25	25	25	25	25	25	25	25	25	25
	D	25	25	25	25	25	25	25	25	25	25
	C	25	25	25	25	25	25	25	25	25	25
	B	25	25	25	25	25	25	25	25	25	25
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X07 SEE NOTE 10 LEAD FREE OPTION	E	33	7	7	7	7	7	7	7	7	7
	D	36	7	7	7	7	7	7	7	7	7
	C	33	7	7	7	7	7	7	7	7	7
	B	36	7	7	7	7	7	7	7	7	7
	A	33	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X08 SEE NOTE 10 LEAD FREE OPTION	E	4	1	1	1	19	1	1	1	19	1
	D	3	1	1	1	19	1	1	1	1	1
	C	3	1	1	1	19	1	1	1	19	1
	B	3	1	1	1	19	1	1	1	19	1
	A	3	1	1	1	19	1	1	1	19	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X09 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	4	4	4	4	4	4	4	4	4	4
	B	1	2	2	2	2	2	2	1	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X10 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	20
	D	6	6	6	6	6	6	6	6	6	20
	C	6	6	6	6	6	6	6	6	6	20
	B	6	6	6	6	6	6	6	6	6	20
	A	6	6	6	6	6	6	6	6	6	20

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X11 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	4	2	19
	D	2	2	2	2	2	2	2	4	2	19
	C	2	2	2	2	2	2	2	4	2	19
	B	2	2	2	2	2	2	2	4	2	19
	A	2	2	2	2	2	2	2	4	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X12 SEE NOTE 10 LEAD FREE OPTION	E	8	8	8	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	20	20	20	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	8	8	8	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X13 SEE NOTE 10 LEAD FREE OPTION	E	4	4	4	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	19	19	19	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	4	4	4	2	2	2	2	2	2	2

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCJ www.fcjconnect.com	
lfr	ecr no.	dr	date	linear	0.X ±0.3			projection	COPY		
CX					0.XX ±0.13				title		
					.XXX ±.051				METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT		
				angles	0° ±2°			MM scale 1:1	product family		
				dr	T.BRUNGARD 11/19/99				METRAL		
				enrg	M.STRAWSER 11/19/99				code		
				chr	M.STRAWSER 11/19/99			size	dwg no	213	
				appd	M.STRAWSER 02/29/00					85853	
sheet index		revision sheet									



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X14 SEE NOTE 10 LEAD FREE OPTION	E	1	4	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	4	1	4	3	1
	C	1	1	1	4	1	1	1	4	3	1
	B	1	4	1	1	1	1	1	4	3	1
	A	1	1	1	1	1	4	1	4	1	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X15 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	4	1	1	1	4	1	1
	D	1	4	1	1	1	1	4	1	1	1
	C	1	1	1	1	4	1	1	1	4	1
	B	1	1	4	1	1	1	1	4	1	1
	A	1	1	1	1	1	4	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X16 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	3	3	1	3	1
	D	1	1	1	1	1	3	3	1	3	1
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X17 SEE NOTE 10 LEAD FREE OPTION	E	1	4	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	4	1	4	3	1
	C	1	1	1	4	1	1	1	4	3	1
	B	1	4	1	1	1	1	1	4	3	1
	A	1	1	1	1	1	4	1	4	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X18 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	4	1	1	1	4	1	1
	D	1	4	1	1	1	1	4	1	1	1
	C	1	1	1	1	4	1	1	1	4	1
	B	1	1	4	1	1	1	1	4	1	1
	A	4	4	1	1	1	4	1	1	1	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X19 SEE NOTE 10 LEAD FREE OPTION	E	25	25	25	25	25	25	25	25	25	25
	D	25	25	25	25	25	25	25	25	25	25
	C	25	25	25	25	25	25	25	25	25	25
	B	25	25	25	25	25	25	25	25	25	25
	A	25	25	25	25	25	25	25	25	25	25

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X20 SEE NOTE 10 LEAD FREE OPTION	E	3	2	2	2	2	2	3	2	2	2
	D	3	2	2	2	2	2	2	2	2	3
	C	3	2	2	2	4	4	4	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X21 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	19
	D	2	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	19
	A	2	2	2	2	2	4	2	4	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X22 SEE NOTE 10 LEAD FREE OPTION	E	4	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	19	19	19	2	19	2	2	2	2	2
	B	2	2	2	2	4	2	2	2	2	2
	A	4	2	2	2	4	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X23 SEE NOTE 10 LEAD FREE OPTION	E	49	49	49	49	49	49	49	49	49	49
	D	49	49	49	49	49	49	49	49	49	49
	C	49	49	49	49	49	49	49	49	49	49
	B	49	49	49	49	49	49	49	49	49	49
	A	49	49	49	49	49	49	49	49	49	49

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X24 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	20
	D	6	6	6	6	6	6	6	6	6	20
	C	6	6	6	6	6	6	6	6	6	20
	B	6	6	6	6	6	6	6	6	6	20
	A	6	6	6	6	6	8	6	8	6	20

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X25 SEE NOTE 10 LEAD FREE OPTION	E	8	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	20	20	20	6	6	20	6	6	6	6
	B	6	6	6	6	6	8	6	6	6	6
	A	8	6	6	6	6	8	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X26 SEE NOTE 10 LEAD FREE OPTION	E	1	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
CX					0.XX ±0.13					METRAL SIGNAL HEADER	
				angles	.XXX ±.051					2 MOD, 5 ROW PRESS-FIT	
					0° ±2°						
				dr	T.BRUNGARD	11/19/99					product family
				enrg	M.STRAWSE	11/19/99					METRAL
				chr	M.STRAWSE	11/19/99					code
				appd	M.STRAWSE	02/29/00					213
sheet		revision								sheet	
index		sheet								4	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X27 SEE NOTE 10 LEAD FREE OPTION	E	5	7	7	7	7	7	7	7	7	7
	D	7	7	7	7	7	7	7	7	7	7
	C	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X28 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	-	2	-	2
	D	2	2	2	2	2	2	-	-	-	-
	C	2	2	2	2	2	2	2	2	-	2
	B	2	2	2	2	2	2	-	-	-	-
	A	2	2	2	2	2	2	-	2	-	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X29 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-
	D	-	-	-	-	-	-	-	-	-	-
	C	2	-	2	-	2	-	2	-	2	-
	B	-	-	-	-	-	-	-	-	-	-
	A	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X30 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	3	19	19	3
	D	-	-	-	-	-	-	3	19	19	3
	C	2	-	2	-	2	-	3	19	19	3
	B	-	-	-	-	-	-	3	19	19	3
	A	2	-	2	-	2	-	3	19	19	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X31 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	4	2	2	2
	D	-	-	-	-	-	-	4	2	2	2
	C	2	-	2	-	2	-	4	2	2	2
	B	-	-	-	-	-	-	4	2	2	2
	A	2	-	2	-	2	-	4	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X32 SEE NOTE 10 LEAD FREE OPTION	E	20	7	7	7	7	20	7	7	7	6
	D	20	7	7	7	7	20	7	7	7	6
	C	20	7	7	7	7	20	7	7	7	6
	B	20	7	7	7	7	20	7	7	7	6
	A	20	7	7	7	7	20	7	7	7	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X33 SEE NOTE 10 LEAD FREE OPTION	E	20	7	7	7	7	20	7	7	7	7
	D	20	7	7	7	7	20	7	7	7	7
	C	20	7	7	7	7	20	7	7	7	7
	B	20	7	7	7	7	20	7	7	7	7
	A	20	7	7	7	7	20	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X34 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	2	2	2
	D	-	-	-	-	-	-	2	2	2	2
	C	2	-	2	-	2	-	2	2	2	2
	B	-	-	-	-	-	-	2	2	2	2
	A	2	-	2	-	2	-	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X35 SEE NOTE 10 LEAD FREE OPTION	E	19	3	3	3	3	3	19	3	3	2
	D	19	3	3	3	3	3	19	3	3	2
	C	19	3	3	3	3	3	19	3	3	2
	B	19	3	3	3	3	3	19	3	3	2
	A	19	3	3	3	3	3	19	3	3	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X36 SEE NOTE 10 LEAD FREE OPTION	E	19	3	3	3	3	3	19	3	3	3
	D	19	3	3	3	3	3	19	3	3	3
	C	19	3	3	3	3	3	19	3	3	3
	B	19	3	3	3	3	3	19	3	3	3
	A	19	3	3	3	3	3	19	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X37 SEE NOTE 10 LEAD FREE OPTION	E	1	-	1	-	1	-	1	-	1	-
	D	-	1	-	1	-	1	-	1	-	1
	C	1	-	1	-	1	-	1	-	1	-
	B	-	1	-	1	-	1	-	1	-	1
	A	1	-	1	-	1	-	1	-	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X38 SEE NOTE 10 LEAD FREE OPTION	E	19	19	19	19	-	19	-	19	-	19
	D	19	19	19	19	-	19	-	19	-	19
	C	19	19	19	19	-	19	-	19	-	19
	B	19	19	19	19	-	19	-	19	-	19
	A	19	19	19	19	-	19	-	19	-	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X39 SEE NOTE 10 LEAD FREE OPTION	E	3	3	7	3	3	7	7	7	7	7
	D	3	3	7	3	3	7	7	7	7	7
	C	3	7	7	7	3	7	7	7	7	7
	B	3	3	3	3	3	7	7	7	7	7
	A	3	3	3	3	3	3	3	3	3	3

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT
CX					0.XX ±0.13				
					.XXX ±.051				
				angles	0° ±2°			product family	METRAL
				dr	T.BRUNGARD 11/19/99				
				engr	M.STRAWSER 11/19/99				
				chr	M.STRAWSER 11/19/99	scale	A	size	dwg no
				appd	M.STRAWSER 02/29/00				
sheet	revision								
index	sheet								



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X40 SEE NOTE 10 LEAD FREE OPTION	E	4	4	4	4	4	4	4	4	4	4
	D	4	4	4	4	4	4	4	4	4	4
	C	4	4	4	4	4	4	4	4	4	1
	B	4	4	4	4	4	4	4	4	4	4
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X41 SEE NOTE 10 LEAD FREE OPTION	E	3	-	3	3	-	3	3	-	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X42 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	1	1	1	1
	D	2	2	2	2	2	2	1	1	1	1
	C	1	1	1	1	1	1	2	2	2	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X43 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	5	5	5	5
	D	2	2	2	2	2	2	5	5	5	5
	C	1	1	1	1	1	1	6	6	6	5
	B	1	1	1	1	1	1	5	5	5	5
	A	1	1	1	1	1	1	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X44 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	5	5	5	5
	D	6	6	6	6	6	6	5	5	5	5
	C	5	5	5	5	5	5	6	6	6	5
	B	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X45 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	5	5	6	6	6	5
	B	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X46 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	1	2	2	2	2	2
	D	2	2	2	2	1	2	2	2	2	2
	C	3	3	3	3	3	3	3	3	3	3
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X47 SEE NOTE 10 LEAD FREE OPTION	E	-	5	5	-	5	5	-	5	5	-
	D	-	5	5	-	5	5	-	5	5	-
	C	-	5	5	-	5	5	-	5	5	-
	B	-	5	5	-	5	5	-	5	5	-
	A	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X48 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	3	2	2	2
	D	2	2	2	2	2	2	3	2	2	2
	C	2	2	2	2	2	2	3	2	2	2
	B	2	2	2	2	2	2	3	2	2	2
	A	2	2	2	2	2	2	3	2	2	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X49 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	2	2	2	2
	D	1	1	1	1	1	1	2	2	2	2
	C	1	1	2	2	2	2	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X50 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	5	2	2	2	2
	D	5	5	5	5	5	5	2	2	2	2
	C	5	5	6	6	6	6	1	1	1	1
	B	5	5	5	5	5	5	1	1	1	1
	A	5	5	5	5	5	5	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X51 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	5	6	6	6	6
	D	5	5	5	5	5	5	6	6	6	6
	C	5	5	6	6	6	6	5	5	5	5
	B	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X52 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	19	19	19	19
	D	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	19	19	19	19
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	19	19	19	19

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCJ www.fcjconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT
CX					0.XX ±0.13				
					.XXX ±.051				
				angles	0° ±2°			product family	METRAL
				dr	T.BRUNGARD 11/19/99				
				engr	M.STRAWSER 11/19/99				
				chr	M.STRAWSER 11/19/99	scale	A	size	dwg no
				appd	M.STRAWSER 02/29/00				
sheet	revision								
index	sheet								



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X53 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	-	-	-	-	-	1
	D	-	1	1	-	-	-	-	-	-	1
	C	-	-	-	-	-	-	-	-	-	-
	B	-	1	1	-	-	1	-	1	1	1
	A	-	1	1	-	-	1	-	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X54 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	-	1	-	1	-	1
	D	1	1	1	1	-	1	-	1	-	1
	C	1	1	1	1	-	1	-	1	-	1
	B	1	1	1	1	-	1	-	1	-	1
	A	1	1	1	1	-	1	-	1	-	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X55 SEE NOTE 10 LEAD FREE OPTION	E	2	19	19	19	19	19	19	19	19	19
	D	2	19	19	19	19	19	19	19	19	19
	C	2	19	19	19	19	19	19	19	19	19
	B	2	19	19	19	19	19	19	19	19	19
	A	2	19	19	19	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X56 SEE NOTE 10 LEAD FREE OPTION	E	19	19	19	19	-	19	-	19	-	19
	D	19	19	19	19	-	19	-	19	-	19
	C	19	19	19	19	-	19	-	19	-	19
	B	19	19	19	19	-	19	-	19	-	19
	A	19	19	19	19	-	19	-	19	-	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X57 SEE NOTE 10 LEAD FREE OPTION	E	-	19	-	-	19	-	19	-	19	19
	D	-	19	-	-	19	-	19	-	19	19
	C	-	19	-	-	19	-	19	-	19	19
	B	-	19	-	-	19	-	19	-	19	19
	A	-	19	-	-	19	-	19	-	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X58 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	-	-	-	-	-	1
	D	-	1	1	-	-	-	-	-	-	1
	C	-	-	-	-	-	-	-	-	-	-
	B	-	1	1	-	1	1	-	1	1	1
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X59 SEE NOTE 10 LEAD FREE OPTION	E	3	-	3	3	3	3	3	3	3	3
	D	3	-	3	3	3	3	3	3	3	3
	C	-	-	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X60 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	19	-	19	-	2	-	19
	D	2	2	2	19	-	19	-	2	-	19
	C	2	2	2	19	-	19	-	2	-	19
	B	2	2	2	19	-	19	-	2	-	19
	A	2	2	2	19	-	19	-	2	-	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X61 SEE NOTE 10 LEAD FREE OPTION	E	19	2	2	2	2	2	2	2	2	2
	D	19	2	2	2	2	2	2	2	2	2
	C	19	2	2	2	2	2	2	2	2	2
	B	19	2	2	2	2	2	2	2	2	2
	A	19	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X62 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	20	-	20	-	6	-	20
	D	6	6	6	20	-	20	-	6	-	20
	C	6	6	6	20	-	20	-	6	-	20
	B	6	6	6	20	-	20	-	6	-	20
	A	6	6	6	20	-	20	-	6	-	20

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X63 SEE NOTE 10 LEAD FREE OPTION	E	20	6	6	6	6	6	6	6	6	6
	D	20	6	6	6	6	6	6	6	6	6
	C	20	6	6	6	6	6	6	6	6	6
	B	20	6	6	6	6	6	6	6	6	6
	A	20	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X64 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	-	-	-	2	2	-	-	-	2
	A	2	-	2	-	-	2	2	-	-	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X65 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	6	5
	D	5	5	6	5	5	5	5	5	6	5
	C	5	5	6	5	5	5	5	5	6	5
	B	5	5	6	5	5	5	5	5	6	5
	A	5	5	6	5	5	5	5	5	6	5

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCJ	
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		www.fcjconnect.com	
CX				linear	0.XX ±0.13	projection		title	
				angles	.XXX ±.051			METRAL SIGNAL HEADER	
				dr	T.BRUNGARD 11/19/99			2 MOD, 5 ROW PRESS-FIT	
				enrg	M.STRAWSE 11/19/99	MM		product family	
				chr	M.STRAWSE 11/19/99	scale		METRAL	
				appd	M.STRAWSE 02/29/00	1:1		code	
sheet	revision							213	
index	sheet							7	
cage code								22526	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X66 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	6	5
	D	5	5	6	5	5	5	5	5	6	5
	C	5	5	6	5	5	5	5	5	6	5
	B	5	5	6	5	5	5	5	5	6	5
	A	5	5	6	5	5	5	5	5	6	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X67 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	5	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	20	20
	B	6	6	6	6	6	6	6	6	20	6
	A	6	6	6	6	6	6	6	6	20	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X68 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	3	2
	C	2	2	2	2	2	2	2	3	3	2
	B	2	2	2	2	2	2	2	3	3	2
	A	2	2	2	2	2	2	2	3	3	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X69 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	4	2	2	2	2	2
	D	2	2	2	2	4	2	2	2	2	2
	C	2	2	2	2	4	4	4	4	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X70 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	4	2	2	2	2	2
	D	2	2	2	2	4	2	2	2	2	2
	C	2	2	2	2	4	2	2	2	2	2
	B	2	2	2	2	4	2	2	2	2	2
	A	2	2	2	2	4	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X71 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	3	2	2	2	2
	D	2	2	2	2	2	3	2	2	2	2
	C	2	2	2	2	2	3	2	2	2	2
	B	-	-	-	-	2	2	3	2	2	2
	A	2	2	2	2	2	3	2	2	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X72 SEE NOTE 10 LEAD FREE OPTION	E	1	4	4	4	19	4	2	19	19	2
	D	1	4	4	4	19	4	2	19	19	2
	C	19	4	4	4	19	4	2	19	19	2
	B	3	4	4	4	19	4	2	19	19	2
	A	3	4	4	4	19	4	2	19	19	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X73 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	6	5	5
	D	5	5	6	5	5	5	5	6	5	5
	C	1	1	6	1	5	5	5	6	5	5
	B	5	5	6	5	5	5	5	6	5	5
	A	5	5	6	5	5	5	5	6	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X74 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	3	3	2
	D	2	2	2	2	2	2	2	3	3	2
	C	2	2	2	2	2	2	2	3	3	2
	B	2	2	2	2	2	2	2	3	3	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X75 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X76 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	3	1	1	1	1
	D	1	1	1	1	1	3	1	1	1	1
	C	1	1	1	1	1	3	1	1	1	1
	B	1	1	1	1	1	3	1	1	1	1
	A	1	1	1	1	1	3	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X77 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	1	2	2	2	2	1	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X78 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	1	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com	
CX				linear	0.XX ±0.13	projection		title	
				angles	.XXX ±.051			METRAL SIGNAL HEADER	
				dr	T.BRUNGARD 11/19/99			2 MOD, 5 ROW PRESS-FIT	
				enrg	M.STRAWSE 11/19/99	MM		product family	
				chr	M.STRAWSE 11/19/99	scale		METRAL	
				appd	M.STRAWSE 02/29/00	1:1		code	
sheet	revision							213	
index	sheet							8	
								cage code	
								22526	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X79 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	7	5	5	5	5
	D	5	5	5	5	5	7	5	5	5	5
	C	5	5	5	5	5	7	5	5	5	5
	B	5	5	5	5	5	7	5	5	5	5
	A	5	5	5	5	5	7	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X80 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	6	5	5	5	5
	D	5	5	5	5	5	6	5	5	5	5
	C	5	6	5	6	6	6	5	5	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X81 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	5	6	6	5	6	5	5	6	5
	B	5	5	5	5	6	5	5	5	5	6
	A	5	5	5	5	6	5	5	5	5	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X82 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X83 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-
	D	2	-	2	-	2	-	2	-	2	-
	C	2	-	2	-	2	-	2	-	2	-
	B	-	2	-	-	2	-	-	2	-	4
	A	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X84 SEE NOTE 10 LEAD FREE OPTION	E	-	-	4	4	4	4	4	4	4	-
	D	-	-	4	4	4	4	2	2	4	-
	C	-	-	4	2	2	4	4	4	4	-
	B	-	-	4	4	4	4	2	2	4	-
	A	-	-	4	4	4	4	4	4	4	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X85 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	2	2	2
	D	-	-	-	-	-	-	2	2	2	2
	C	2	2	2	-	2	2	-	2	2	2
	B	2	2	2	-	2	2	-	2	2	2
	A	2	2	2	-	2	2	-	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X86 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X87 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X88 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1
	B	3	3	3	3	3	3	3	3	3	3
	A	19	19	19	19	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X89 SEE NOTE 10 LEAD FREE OPTION	E	19	19	19	19	19	19	3	19	19	19
	D	3	3	3	3	3	3	3	3	3	3
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X90 SEE NOTE 10 LEAD FREE OPTION	E	3	-	3	3	3	3	3	3	3	3
	D	3	-	3	3	3	3	3	3	3	3
	C	-	-	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X91 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	1	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY	projection	title	METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT		
CX				angles	0.XX ±0.13			product family	METRAL	code	213
					.XXX ±.051			size	dwg no	sheet	9
				dr	0° ±2°			85853			
				enrg	T.BRUNGARD 11/19/99						
				chr	M.STRAWSE 11/19/99						
				appd	M.STRAWSE 02/29/00						
sheet	revision										
index	sheet										



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X92 SEE NOTE 10 LEAD FREE OPTION	E	-	5	5	-	5	5	-	5	5	-
	D	-	5	5	-	5	5	-	5	5	-
	C	-	5	5	-	5	5	-	5	5	-
	B	-	5	5	-	5	5	-	5	5	-
	A	-	5	5	-	5	5	-	5	5	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X93 SEE NOTE 10 LEAD FREE OPTION	E	8	6	6	6	6	6	6	6	6	6
	D	8	6	6	6	6	6	6	6	6	6
	C	8	6	6	6	6	6	6	6	6	6
	B	8	6	6	6	6	6	6	6	6	6
	A	8	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X94 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	4
	D	2	2	2	2	2	2	2	2	2	4
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X95 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	1	1	-	1	1	-
	D	-	1	1	-	1	1	-	1	1	-
	C	-	1	1	-	1	1	-	1	1	-
	B	-	1	1	-	1	1	-	1	1	-
	A	-	1	1	-	1	1	-	1	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X96 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-
	D	2	-	2	-	2	-	2	-	2	-
	C	2	-	2	-	2	-	2	-	2	-
	B	2	-	2	-	2	-	2	-	2	-
	A	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X97 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	1	2	2	2	2	2	2	2	2	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X98 SEE NOTE 10 LEAD FREE OPTION	E	19	1	2	2	1	2	2	2	2	19
	D	1	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	19
	A	2	1	2	2	2	2	2	2	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X99 SEE NOTE 10 LEAD FREE OPTION	E	2	1	2	2	1	2	2	2	2	19
	D	2	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	19
	A	2	1	2	2	2	2	2	2	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X100 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	1	1	1	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X101 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	8	20	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	20	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X102 SEE NOTE 10 LEAD FREE OPTION	E	4	4	3	4	3	4	4	4	3	4
	D	4	4	3	4	3	4	4	4	3	4
	C	4	4	4	4	4	4	4	4	4	4
	B	4	4	2	4	2	4	4	2	4	4
	A	4	4	2	4	2	4	4	2	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X103 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	4	3	4	3	4	3	3
	D	3	3	3	4	3	4	3	4	3	3
	C	3	3	3	4	2	4	3	4	3	3
	B	3	3	3	4	2	4	2	4	3	3
	A	3	3	3	4	2	4	2	4	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X104 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	2	3	3	3	3
	D	3	3	3	3	3	2	3	3	3	3
	C	3	3	3	3	3	2	3	3	3	3
	B	3	3	3	3	3	2	3	3	3	3
	A	3	3	3	3	3	2	3	3	3	3

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
CX					0.XX ±0.13					METRAL SIGNAL HEADER	
					.XXX ±.051					2 MOD, 5 ROW PRESS-FIT	
				angles	0° ±2°					product family	
				dr	T.BRUNGARD	11/19/99					METRAL
				enrg	M.STRAWSE	11/19/99					code
				chr	M.STRAWSE	11/19/99					213
				appd	M.STRAWSE	02/29/00					sheet
sheet		revision								10	
index		sheet									



A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X105 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	3	3	3	3	3	3	3
	D	2	2	2	3	3	3	3	3	3	3
	C	2	2	2	3	3	3	3	3	3	3
	B	2	2	2	3	3	3	3	3	3	3
	A	2	2	2	3	3	3	3	3	3	3
85853-X106 SEE NOTE 10 LEAD FREE OPTION	E	3	7	7	7	7	7	8	7	8	7
	D	3	7	7	7	7	7	8	7	8	7
	C	3	7	7	7	7	7	8	7	8	7
	B	3	7	7	7	7	7	8	7	8	7
	A	3	7	7	7	7	7	8	7	8	7
85853-X107 SEE NOTE 10 LEAD FREE OPTION	E	3	8	7	7	7	7	7	7	7	7
	D	3	8	7	7	7	7	7	7	7	7
	C	3	8	7	7	7	7	7	7	7	7
	B	3	8	7	7	7	7	7	7	7	7
	A	3	8	7	7	7	7	7	7	7	7
85853-X108 SEE NOTE 10 LEAD FREE OPTION	E	7	8	7	8	7	8	7	8	7	8
	D	7	8	7	8	7	8	7	8	7	8
	C	8	8	8	8	8	8	8	8	8	8
	B	6	8	6	8	6	8	6	8	6	8
	A	6	8	6	8	6	8	6	8	6	8
85853-X109 SEE NOTE 10 LEAD FREE OPTION	E	19	1	2	2	1	2	2	2	2	19
	D	1	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	19
	B	19	2	2	2	2	2	2	2	2	19
	A	1	1	2	2	2	2	2	2	2	19

B

1 | 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X110 SEE NOTE 10 LEAD FREE OPTION	E	-	2	-	2	-	2	-	2	-	2
	D	2	-	2	-	2	-	2	-	2	-
	C	-	2	-	2	-	2	-	2	-	2
	B	2	-	2	-	2	-	2	-	2	-
	A	-	2	-	2	-	2	-	2	-	2
85853-X111 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	5	5
	D	5	5	6	5	5	5	6	6	6	6
	C	6	6	6	5	5	5	6	6	6	6
	B	5	5	5	5	5	5	6	6	6	6
	A	6	6	6	6	6	6	5	5	5	5
85853-X112 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	2	1	1	1	1
	D	1	1	1	1	1	2	1	1	1	1
	C	1	1	2	1	1	1	1	1	1	1
	B	1	1	1	1	1	2	1	1	1	1
	A	1	1	1	1	1	2	2	1	1	1
85853-X113 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	4	2	2	4	2	2	4	3	3	4
	C	2	2	4	2	2	4	3	3	4	3
	B	2	4	2	2	4	3	3	4	3	3
	A	2	2	2	2	2	2	2	2	2	3

3 |

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X114 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	4	3	3
	D	3	3	3	3	3	3	3	4	3	3
	C	3	3	3	3	3	3	3	4	3	3
	B	3	3	3	3	3	3	3	4	3	3
	A	3	3	3	3	3	3	3	4	3	3
85853-X115 SEE NOTE 10 LEAD FREE OPTION	E	2	2	1	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
85853-X116 SEE NOTE 10 LEAD FREE OPTION	E	6	6	7	7	6	6	6	7	7	6
	D	6	6	7	7	6	6	6	7	7	6
	C	6	6	7	7	6	6	6	7	7	6
	B	6	6	7	7	6	6	6	7	7	6
	A	6	6	7	7	6	6	6	7	7	6
85853-X117 SEE NOTE 10 LEAD FREE OPTION	E	64	-	64	-	64	-	64	-	64	-
	D	-	64	-	64	-	64	-	64	-	64
	C	64	-	64	-	64	-	64	-	64	-
	B	-	64	-	64	-	64	-	64	-	64
	A	64	-	64	-	64	-	64	-	64	-

A

4

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com		
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
CX					0.XX ±0.13					
					.XXX ±.051					
				angles	0° ±2°	MM	scale	product family	METRAL	
				dr	T.BRUNGARD					11/19/99
				enrg	M.STRAWSE					11/19/99
				chr	M.STRAWSE	11/19/99	size	dwg no	code	
				appd	M.STRAWSE	02/29/00				
sheet	revision									
index	sheet									

B

1 | 2

Pro/E

3 |

cage code 22526

4



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X118 SEE NOTE 10 LEAD FREE OPTION	E	6	-	6	-	6	-	6	-	6	-
	D	-	6	-	6	-	6	-	6	-	6
	C	6	-	6	-	6	-	6	-	6	-
	B	-	6	-	6	-	6	-	6	-	6
	A	6	-	6	-	6	-	6	-	6	-
85853-X119 SEE NOTE 10 LEAD FREE OPTION	E	4	2	2	2	2	2	2	2	2	2
	D	2	2	4	4	2	2	2	2	2	2
	C	19	2	19	2	2	19	2	2	2	2
	B	2	2	2	4	2	4	2	2	2	2
	A	4	2	2	2	2	4	2	2	2	2
85853-X120 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	19	2
	D	2	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	19
	A	2	2	4	4	2	4	2	4	2	19
85853-X121 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	8
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6
85853-X122 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	4
	D	2	2	2	2	2	2	2	2	2	4
	C	2	2	2	2	2	2	2	4	4	2
	B	2	2	2	2	2	2	2	2	2	4
	A	2	2	2	2	2	2	2	1	2	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X123 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	4
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
85853-X124 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	1
85853-X125 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	19	19	19	19	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	1
85853-X126 SEE NOTE 10 LEAD FREE OPTION	E	2	6	6	6	6	6	2	2	2	2
	D	2	6	6	6	6	6	2	2	2	2
	C	2	6	6	6	6	6	2	2	2	2
	B	2	6	6	6	2	1	6	2	2	2
	A	2	6	6	6	6	6	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X127 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	19	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
85853-X128 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	3	19
	D	2	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	19	19	2	2
	B	2	2	2	2	2	2	2	2	2	19
	A	2	2	2	2	2	2	2	2	1	19
85853-X129 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	3
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
85853-X130 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	7
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCJ		www.fcjconnect.com			
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	METRAL SIGNAL HEADER				
CX					0.XX ±0.13				2 MOD, 5 ROW PRESS-FIT				
					.XXX ±.051								
				angles	0° ±2°	MM	scale	product family	METRAL		code		
				dr	T.BRUNGARD				11/19/99	size		dwg no	213
				enrg	M.STRAWSE				11/19/99				
				chr	M.STRAWSE	11/19/99							
				appd	M.STRAWSE	02/29/00					sheet		
											12		
sheet	revision												
index	sheet												



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X131 SEE NOTE 10 LEAD FREE OPTION	E	9	-	9	-	9	-	9	-	9	-
	D	9	-	9	-	9	-	9	-	9	-
	C	-	-	-	-	-	-	-	-	-	-
	B	9	-	9	-	9	-	9	-	9	-
	A	9	-	9	-	9	-	9	-	9	-
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X132 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	5	5	5	5	5	5	6	6	6	6
	A	5	5	5	5	5	5	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X133 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	7	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X134 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	1	1	2	3
	D	2	2	2	2	2	2	1	1	2	3
	C	2	2	2	2	2	2	1	1	2	3
	B	2	2	2	2	2	2	1	1	2	3
	A	2	2	2	2	2	2	1	1	2	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X135 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	1	1	1	1
	D	2	2	2	2	2	2	1	1	1	1
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	1	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X136 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	3	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X137 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	-	-	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X138 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	3	2	2	2	3	2	2
	D	2	2	2	3	2	2	2	3	2	2
	C	2	2	2	2	3	2	2	2	3	2
	B	2	2	2	2	2	3	2	2	3	2
	A	2	2	2	2	2	1	2	2	3	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X139 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	19	19


METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X140 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	4	2	2	2	2	2	4	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X141 SEE NOTE 10 LEAD FREE OPTION	E	64	64	64	64	64	64	64	64	64	64
	D	64	64	64	64	64	64	64	64	64	64
	C	67	64	64	64	64	64	67	64	64	64
	B	64	64	64	64	64	64	64	64	64	64
	A	64	64	64	64	64	64	64	64	64	64
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X142 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	1	1
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X143 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	1
	C	2	2	2	2	2	2	2	2	2	1
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCJ		www.fcjconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
CX					0.XX ±0.13					METRAL SIGNAL HEADER	
				angles	.XXX ±.051					2 MOD, 5 ROW PRESS-FIT	
				dr	T.BRUNGARD 11/19/99					product family	
				enrg	M.STRAWSE 11/19/99			size		METRAL	
				chr	M.STRAWSE 11/19/99			dwg no		code	
				appd	M.STRAWSE 02/29/00			A		213	
sheet index		revision sheet						scale		sheet	
								1:1		13	
										cage code	
										22526	

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.



METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X144 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	1	2	2	2	2	2	2
	D	2	2	2	2	2	1	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	1	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X145 SEE NOTE 10 LEAD FREE OPTION	E	7	6	6	6	6	6	6	6	6	6	6	6
	D	7	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6
	B	7	6	6	6	6	6	6	6	6	6	6	6
	A	7	6	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X146 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	7	6	6	6	6	5	5	5	5	5	5	5
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X147 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	5	6	6	6
	D	6	6	6	6	6	6	6	6	5	6	5	6
	C	6	6	6	6	6	6	6	6	5	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	5

mat'l code				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ±0.3	projection		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
CX			0.XX ±0.13						
			.XXX ±.051						
			0° ±2°						
				angles					
				dr	T.BRUNGARD	11/19/99		product family	
				enr	M.STRAWSER	11/19/99		METRAL	
				chr	M.STRAWSER	11/19/99		size	dwg no
				appd	M.STRAWSER	02/29/00		A	85853
sheet		revision						code	
index		sheet						213	
								sheet	
								14	

cage code 22526

Pro/E

PDM: Rev: CX

STATUS: Released

Printed: Jan 17, 2011



PRODUCT NUMBER
85853-XYX OR 85853-XXXX
85853-XYXLF OR 85853-XXXXLF

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
 - BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
 - PIN MATERIAL:
PHOSPHOR BRONZE.
 - PLATING ON PRESS-FIT TAIL:
85853-XYX IS SnPb
85853-XYXLF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE BELOW.
 - PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
 - ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP
 - PRODUCT SPECIFICATION GS-12-180
APPLICATION SPECIFICATION BUS-20-073
 - AFTER INSERTION INTO CIRCUIT BOARD WITH
QUALIFIED TOOL.
 - THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.
- ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-NI--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-NI---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.
- FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX.
EXAMPLE: 85853-X0ILF

PLATING IN CONTACT AREA		NOTES
DASH NUMBER	PERFORMANCE LEVEL	-
-PYY OR -PYXX	0.25 um GOLD MIN.	-
-NIYY OR -NIYXX	TELCORDIA CO (NXT)	-
-N5YY OR N5YXX	TELCORDIA UE (NXT)	-
-1YY OR -1YXX	TELCORDIA CO	-
-2YY OR -2YXX	TELECOM CLASS	-
-3YY OR -3YXX	IEC CLASS I	-
-5YY OR -5YXX	TELCORDIA UE	-
-NIYXLF OR -NIYXXLF	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 9
-N5YXLF OR N5YXXLF	TELCORDIA UE (NXT)	SEE NOTE 9
-1YXLF OR -1YXXLF	TELCORDIA CO IEC CLASS I	SEE NOTE 9
-2YXLF OR -2YXXLF	TELECOM CLASS	SEE NOTE 9
-5YXLF OR -5YXXLF	TELCORDIA UE	SEE NOTE 9

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
CX					0.XX ±0.13	projection			
					.XXX ±.051				
				angles	0° ±2°				
				dr	T.BRUNGARD	11/19/99	MM		product family
				enrg	M.STRAWSE	11/19/99			METRAL
				chr	M.STRAWSE	11/19/99	scale		code
				appd	M.STRAWSE	02/29/00	1:1		213
sheet	revision						A		sheet
index	sheet								15