



Features:

Material and Finish:

Zinc-Die-Cast, Nickel Plated

Temperature Range:

-40°C to +120°C

Cable Diameter:

4.0-13.0mm

Attenuation Factor:

>40 DB Between 30Mhz and 1 Ghz

Requirements:

VDE 0871 FCC 20/80/89/336/EU

No. of Contacts:

09, 15, 25, 37

Black Anodized Version on Request

09-poles only with one knurled screw available

Dimensions

No. of Contacts	A1	A	B	C	D	E
09	12.7	-----	31	19.3	29.8	31.2
15	-----	33.3	39.5	20.7	29.8	35.2
25	-----	47	53.2	20.8	29.8	35.2
37	-----	63.5	69.7	20.8	29.8	35.2



Description

Name :

AMET-X-RS-45

Hoods for D-Sub-Connectors

ASSMANN
Electronic Components

THIS DRAWING IS UNPUBLISHED

© Copyright 2005 by Assmann Electronic Components All International Rights Reserved

This drawing is a controlled document for Assmann Electronics, Inc. It is subject to change and the controlling engineering organization should be contacted for the latest revision.