






- THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
 - MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA
 - STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS
 - PACKAGE STAMPED M24308/2-294F
 - THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT M24308/10 DR TE # 205090
- 6 MFG'S PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- 7 UL/CSA DESIGNATION STAMPED IN THIS AREA.

OBSOLETE	BRASS	205418-2
	STEEL PER ASTM-A-109	205418-1
	SHELL MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 6-4-09	TE Connectivity	
DIMENSIONS: INCHES		CHK R. LEASE 6-4-09	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. LEASE 6-4-09	RCPT. ASSY. AMPLIMITE, 25 POSN., SIZE 3, SERIES 109, W/DUAL FLOATING BUSHINGS	
0 PLC ± -		PRODUCT SPEC	—	
1 PLC ± -		APPLICATION SPEC	—	
2 PLC ± -		—	—	
3 PLC ± .005		—	—	
4 PLC ± -		—	—	
ANGLES ± ° 30'		—	—	
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT —	SIZE A1	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1
		REV P		