

181-00239

Article Number: 181-00239

Slotted Wall Wiring Duct, 2" X 5", Adhesive, PVC, Gray, 30ft/Box



Download drawing

Download spec sheet

Base Data

Local Order Number	181-00239
Type	SLA2X5
Color	Gray (GY)
Features and Benefits	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
Product Description	Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "Ts".
Short Description	Slotted Wall Wiring Duct, 2" X 5", Adhesive, PVC, Gray, 30ft/Box

Product Dimensions

Length L (Imperial)	6.0 ft
Length L (Metric)	1.83 m
Width W (Imperial)	2.0 "
Width W (Metric)	50.8 mm
Width W2 (Imperial)	2.0 "
Width W2 (Metric)	50.8 mm
Width W3 (Imperial)	0.4 "
Width W3 (Metric)	10.2 mm
Width W4 (imperial)	1.0 "
Width W4 (metric)	25.4 mm
Width W5 (imperial)	4.6 "
Width W5 (metric)	116.8 mm
Width W6 (imperial)	0.5 "
Width W6 (metric)	12.7 mm
Height H (Imperial)	5.07 "
Height H (Metric)	128.8 mm
Mounting Hole Centers (Imperial)	4.0 "

Logistics and Packaging

Quantity Per	box
Package Quantity	30.0 ft

Package Quantity (Metric) 9.1 m

Carton Quantity 30.0 ft

Material and Specifications

Material Polyvinylchloride (PVC)

Material Shortcut PVC

Flammability self-extinguishing

Operating Temperature +122°F (+50°C)

ROHS Compliant Yes

Certification/Specification CSA
UL

UL Listed (US and Canada) No

UL Recognized (US and Canada) No

UL Recognized (US) Yes