

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING		Amphenol Connex					
					APPROVALS	DATE					
					DRAWN	GRS	03/26/09	PART DESCRIPTION			
6	HEX NUT	BRASS	NICKEL		1	CHECKED		SMA FEMALE TO TNC BULKHEAD FEMALE ADAPTER			
5	LOCK WASHER	PHOS. BRONZE	NICKEL		1	ISSUED		PART NO.			
4	GASKET	SILICONE	RED		1	SHEET	1 OF 1	242178			
3	CONTACT PIN	BER. COPPER	GOLD		1			DWG. NO.			
2	INSULATOR	PTFE	NATURAL		1	CAD FILE		REV. A		SIZE A	SCALE NA
1	BODY	BRASS	NICKEL	1	C:/242/242178.DWG		242178.DWG				
	DESCRIPTION	MATERIAL	FINISH	QTY							