



FEATURES:

- Provides protection from over current.
- Accepts standard .25 inch (6.4mm) diameter SFE and AGC fuses (fuse not included).
- Mates to Model #1581, 2854 or any standard banana jack.
- Vertical and cross stackable.

MATERIALS:

Conn: Stacking Banana Plug.

Material: Brass body, Beryllium Copper spring, nickel plated.

Insulation: Polypropylene.

Wire: 18 AWG, 65 x 36 t.c., PVC insulated, 3.7 (.144) O.D. Fuse holder, brass, tin plated.

Insulation: PVC. Accepts 6.4 (.25) dia. SFE and AGC fuses (not included).

RATINGS:

Operating Temperature: +55°C. (+131°F.) Max.

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 5000 WVDC Max.

Current: 15 Amperes

ORDERING INFORMATION: Model 4274-XX-*

XX = Cable Lengths, Standard Lengths: 24" (610), and 36" (914).

Additional lengths can be quoted upon request.

*= Color, -0 Black, -2 Red

Ordering Example: 4274-36-2 Indicates 36" in length, color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Model 4274 Multi-Stacking Banana Plug Patch Cord with In-Line Fuse Holder

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA