








NOTES:

MATERIALS:

RECEPTACLE SHELL: NICKEL PLATED BRASS
CONTACTS: GOLD/NICKEL OVER COPPER ALLOY
MALE INSERT: YELLOW PVC
FEMALE INSERT: YELLOW TPE
LOCKNUT: NICKEL PLATED BRASS
THRUST WASHER: NYLON
GASKET: BLACK NEOPRENE

ELECTRICAL:

CURRENT RATING: 8AMP MAX
VOLTAGE RATING: 600V

MECHANICAL:

TEMPERATURE RANGE: -20° TO 60°C
INGRESS PROTECTION: IP 67

AGENCY CERTIFICATIONS:

AGENCY: CSA CERTIFIED

ADD KO & WIRE DIAGRAM	
EC NO: IGC2017-0838	DRWN: MZIELINS 2017/03/07
CHKD: ---	APPR: BWOODMAN 2008/10/27
REV	DESCRIPTION
B	

QUALITY SYMBOLS
▽=0
▽C=0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±---
1 PLACE	±---	±---
ANGULAR ±---°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE IN/MM	
DRAWN BY	DATE
BW	2009/07/28
CHECKED BY	DATE
TW	2009/07/29
APPROVED BY	DATE
JFMURPHY	2008/10/27
MATERIAL NO.	
SIZE A	

MATERIAL NUMBER		OLD PART NUMBER	
130013-0541		1R5030	
SCALE ---	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
TITLE MINI-CHANGE RECEPTACLE 5 POLE MA/FE PASS-THRU -----			
 MOLEX INCORPORATED			
DOCUMENT NO. SD-130013-012		SHEET NO. 1 OF 1	
CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX O SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			