

Spiral wrap Cable protection systems




- For protection of bundles from 4 mm to 130 mm
- Install gapped for greater flexibility or butted for maximum abrasion resistance, insulation and rigidity
- Counter-clockwise cut
- Delivered in bags with Euroslot
- Available in natural and UV-resistant black Polyethylene


Technical Information

Material	Polyethylene
Temperature range	-40°C to +100°C
Colour	Natural and UV-resistant black
Flammability rating	UL 94 HB
Other properties	UV-resistant (black), Halogen free, Silicone free

Nominal thickness



Pitch



Product Ref.	Colour	Outer diameter [mm]	Pitch [mm]	Nominal thickness [mm]	Min. - max. bundle ø [mm]	Length [m]
SRPE-6-9	natural	6.0	7.0	0.5	4 - 50	10
SRPE-8-9	natural	8.0	10.8	0.5	6 - 60	10
SRPE-10-9	natural	10.0	11.4	0.8	7.5 - 60	10
SRPE-12-9	natural	12.0	13.9	0.9	9 - 65	10
SRPE-15-9	natural	15.0	15.0	1.0	12 - 70	10
SRPE-19-9	natural	19.0	18.2	1.3	15 - 100	10
SRPE-24-9	natural	24.0	19.6	1.5	20 - 130	10
SRPE-6-0	UV-resistant black	6.0	7.0	0.5	4 - 50	10
SRPE-8-0	UV-resistant black	8.0	10.8	0.5	6 - 60	10
SRPE-10-0	UV-resistant black	10.0	11.4	0.8	7.5 - 60	10
SRPE-12-0	UV-resistant black	12.0	13.9	0.9	9 - 65	10
SRPE-15-0	UV-resistant black	15.0	15.0	1.0	12 - 70	10
SRPE-19-0	UV-resistant black	19.0	18.2	1.3	15 - 100	10
SRPE-24-0	UV-resistant black	24.0	19.6	1.5	20 - 130	10