

WCY60

WCY60

WCY60 : WEJTAP CONN YEL



ACTIVE

RoHS compatible

BURNDY® PRODUCTS

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Specifications

Download document

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Conductor Size (Run - Diameter)	0.722 to 0.95		
Conductor size (Run - Max)	556.5-18/1		
Conductor size (Run - Min)	5565		
Conductor Size (Run - mm)	18 mm² to 24 mm²		
Conductor Size (Run)	556.5 556.5-18/1		
Conductor size (Tap - Max)	556.5-18/1		
Conductor size (Tap - Min)	5565		
Conductor Size (Tap)	556.5 556.5-18/1		
Conductor Type (Run)	ACSR AAC		
Wire Size	AWG		
Wire Size (Tap - Diameter - in)	0.722 to 0.95		
Wire Size (Tap - mm)	18 mm² to 24 mm²		
Wire Type (Tap)	ACSR AAC		
Physical			
Color Code	Yellow		
Approvals / Certifications			
UL Listed	No		
CSA Certified	No		
Other Features			
Installation Tool	WTY		
Booster	WPBY Box 25		
UPC	78181087440		
Keyword	wejtap		