

5 to 15W AC-DC Board Mount Power Supplies



- ◆ Small Size and lightweight
- ◆ PC board Mountable
- ◆ Low Cost
- ◆ Universal Input Voltage
- ◆ UL Class II Approved

RoHS

Key Market Segments & Applications

Factory Automation
Printers and motor drives
Kiosks

Features and Benefits

Feature	Benefit
◆ Small size	◆ Minimizes pcb space
◆ Wide input range	◆ Global use with no manual intervention
◆ No external components needed	◆ Easy to use
◆ Class II UL approved	◆ No ground connection needed

Specifications

MODEL		KPS-5	KPS-10	KPS-15
ITEMS				
Input Voltage range		85 - 264VAC (47 - 440Hz) or 110 - 370VDC		
Inrush Current (115 / 230VAC)	A	20/40		
Input Current (115/230VAC)	A	0.13 / 0.07	0.27 / 0.13	0.4 / 0.2
Temperature Coefficient		±0.05%/°C		
Voltage Accuracy		±1%		
Minimum Load	A	None		
Load Regulation		±1% (10% to 100% load)		
Line Regulation (1)		±0.5%		
Ripple & Noise (2)	mV	1% or 50mV whichever is greater		
Short Circuit Protection	-	Continuous - hiccup mode		
Overvoltage Protection	V	130-150%		
Hold Up Time (Typ@115VAC)	ms	8	16	16
LED Indicator		Green LED = OK		
Operating Temperature		0 to +70°C, derate linearly to 25% load from 40°C to 70°C		
Storage Temperature		-20 to +85°C		
Humidity (non condensing)		10 - 95% RH		
Cooling		Convection		
Withstand Voltage		Input to Output 3kVAC		
Vibration (non operating)		23.52m/s ² (10 - 55Hz: constant sweep 1 min X, Y, Z for 1 hour)		
Shock		< 196.1 m/s ² (20G)		
Safety Agency Approvals	-	UL60950-1, CSA60950-1, EN60950-1, Class II, CE Mark		
Conducted & Radiated EMI		EN55022-B, FCC Class B		
Immunity		EN61000-4 -2, -3, -4, -5, -6		
Weight (Typ)	g (oz)	29g (1oz)	60g (2oz)	80g (2.8oz)
Size (WxLxH; H above pcb)	in.	1.38 x 2.17 x 0.79	1.77 x 2.56 x 0.91	1.89 x 2.75 x 0.91
Warranty		One Year		

Notes:

(1) KPS-5 Measured from 100 - 240VAC


(2) Measured with 0.1uF ceramic & 10uF electrolytic at 20MHz BW

Model Selector (other voltages available)

Model	Output Voltage (V)	Maximum Output (A)	Peak Load (A)(3)	Output Pwr (W)	Effic (%)
KPS5-3R3	3.3	1.25	-	4.1	70
KPS5-5	5.0	1.00	-	5.0	70
KPS5-12	12.0	0.42	-	5.0	70
KPS5-15	15.0	0.33	-	5.0	70
KPS5-24	24.0	0.23	-	5.5	77
KPS10-3R3	3.3	2.50	3.80	8.3	65
KPS10-5	5.0	2.00	2.80	10.0	70
KPS10-12	12.0	0.84	1.20	10.1	75
KPS10-15	15.0	0.67	1.00	10.1	75
KPS10-24	24.0	0.42	0.65	10.1	78
KPS15-3R3	3.3	3.00	4.50	9.9	70
KPS15-5	5.0	3.00	4.50	15.0	73
KPS15-12	12.0	1.25	1.80	15.0	80
KPS15-15	15.0	1.00	1.50	15.0	80
KPS15-24	24.0	0.63	0.95	15.1	82

(3) Average not to exceed max power, <30s, 10%, duty cycle


KPS10 Outline Drawing



Other Lambda Industrial Products

ZP	40W & 60W, 2x4" footprint
NV175	175W, 3x5", 1-5 outputs
ZWS	5 to 240W, single output

KPS5 Outline Drawing



KPS15 Outline Drawing

