





KPP-4P

Material and Finish

Inner Shield: copper alloy,
tin plated

Body: ABS thermoplastic
UL94HB rated
color - black

Insert: Nylon, Black Color
UL94V-2 Rated

Contacts: brass, tin plated

Electrical Characteristics

Contact Rating:
7.5A max. @ 20V DC

Insulation Resistance:
50 Megohms min. at 250V DC

Dielectric Strength:
250 V AC rms for 1 minute

Contact Resistance:
50 milliohms max.



Tolerances	
X.X ± 0.25	
X.XX ± 0.15	
Unless Stated Otherwise	

REVISION	DATE	DESCRIPTION	DRAWN BY	CHECKED BY	UNITS
A8	12/3/02	ECO #02-136	J. Kring	H. MA	mm
A9	11/10/04	ECO#04-061	REVISED BY	CHECK DATE	DATE
A10	4/21/06	ECO#06-028	R. Aguirre	4/24/06	1/11/95

KPP-4P

DC Power Plug

4 position, snap-and-lock type



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KPP-4P-200](#) [KPP-4P](#)