






SECTION A-A
SCALE 2.000



DESCRIPTION	PRODUCT NO.		
KIT	72844-X01LF	72844-X02LF	72844-X03LF
COVER WITH GROUND SPRING	1	1	1
CONTACT STRIP	5	5	5
HEADER	1		
HEADER		1	
HEADER			1

Dimension with oval around are critical dimensions including any attached geometrical tolerance. Other features or stanf-alone geometrical tolerances being critical have a note "CRITICAL FEATUR" below the item.
A symbol x (x: drawing current revision) will be next to any dimension, view or note which has been molded with the current drawing revision

ROHS INFORMATION:

- This product meets European Union Directives and other country regulations as described in GS-22-008.
- The housing will withstand exposure to 260°C peak temperature for 5 second in a wave solder application with a 1.4 mm minimum thick circuit board. see application notes/procedures if they are available.
- Packaging spec: see GS-14-920

www.fciconnect.com			surface 0.8 ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	B.Beirinckx	2002/06/30	ANGULAR	LINEAR	0.X	±0.3	size	Scale			
Eng	G.Nys	2002/06/30			0.XX	±0.1	A4	1.000			
Chr	W.Panis	2002/06/30			0.XXX	±0.05		ECN LS07-0255			
Appr	W.Panis	2002/06/30	Product family				SOFIX		Spec ref		
			title				SOFIX STB SHIELDED I/O				Rev W
			Shielded RA Hdr 4x6 Pos				72844_C				
			catalog no				sheet 2 of 2				