

C-1328
ステンレス製

特徴 Feature

- ねじ頭をキャップでカバーするので安全です。
- キャップを軽く押込むだけの簡単取付け
- サークリップがキャップの溝にはまり、空回りして抜けません。

- This set cap covers a screw head to ensure safety.
- Easy installation: Lightly squeeze the cap onto a screw head.
- The set cap never comes off because its retaining ring snaps into the cap groove and spins freely.

仕様 • 材質: ステンレス鋼(SUS304)

- 表面仕上: 光沢/バレル研磨
- ナットとボルトの取外し防止
- 標準品: • 納期お問合せ下さい
- 取付けると外れませんので取扱に十分注意して下さい。

- ボルトとナットで締付けている配管フランジのような場合は、両側に使用します。キャップはナット側用とボルト側用の二つのタイプがあります。
- 取外し工具を必要とする場合は、ご相談下さい。工具を使用する場合は、Φ60mmの設置面と100mmの高さを設計上設けて下さい。
- キャップと座金のセット価格です。
- C-1328-A-16・B-16は中止品となりました。

Specifications • Material: Stainless steel (SUS304)

- Finish: Gloss barrel polishing
- Preventing the removal of nuts and bolts

Specific use • Handle a set cap with sufficient care. It cannot be removed once it is snapped on.

- Install set caps on both ends of piping flanges fastened using bolts and nuts. Two types of caps are available: those for nuts and for bolts.




- Consult with TAKIGEN if a demounting tool is required. To use a tool, provide an installation area 60mm in diameter and 100mm in height at the design stage.

- These prices are for a set of caps and washers.
- Products C-1328-A-16 and C-1328-B-16 are no longer manufactured.

セットキャップ*

SET CAPS




いたずら防止に高い効果

C-1328-B
(ボルト側用)
Bolt sideC-1328-A
(ナット側用)
Nut side[キャップ側]
Cap[座金側]
Washer

C-1328-A・B・C

C-1328-A・B


C-1328-C



商品番号 Product No.	RoHS CAD	備考 Remarks	ΦD	Φd1	Φd2	Φd3	H1	H2	h	コード Code	単価 Price	量販価格 数量 Quantity	Bulk Price 単価 Price	
C-1328-C-4		M4ねじ用 Countersink	18	4.5			9	8	5.5		23669	¥960	10個~	¥922
C-1328-C-5		M5ねじ用 Countersink	18	5.5			10	8	5.5		23670	¥960	10個~	¥922
C-1328-A-6	●	M6ナット用 Nut	19	7	6.3		14.5	5.5	6以下less	23652	¥1,050	10個~	¥1,019	
C-1328-B-6	● 2D/3D	M6ボルト用 Bolt	19		6.3		14.5	5.5		23653	¥1,050	10個~	¥1,019	
C-1328-A-8	●	M8ナット用 Nut	22.5	8.5	8.2		17.5	6	8以下less	23593	¥1,200	10個~	¥1,164	
C-1328-B-8	●	M8ボルト用 Bolt	22.5		8.2		17.5	6		23594	¥1,200	10個~	¥1,164	
C-1328-A-10	●	M10ナット用 Nut	26.5	10.5	10.3		19.5	6	10以下less	23595	¥1,400	10個~	¥1,358	
C-1328-B-10	●	M10ボルト用 Bolt	26.5		10.3		19.5	6		23596	¥1,400	10個~	¥1,358	
C-1328-A-12	●	M12ナット用 Nut	30	13.5	13		24	6.5	12以下less	23654	¥1,850	10個~	¥1,776	
C-1328-B-12	●	M12ボルト用 Bolt	30		13		24	6.5		23655	¥1,850	10個~	¥1,776	

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。

使用例
Example of application

ラバーフラッシュナット
錆前装錆・周辺機器
ラッピング
ラッピング
ドアキャッチ
スナップロック
コントロールセンター
太陽光関連金具
グレーチング
ロップ
工業用錆前
電磁波対策
パッキン
窓枠・カードホルダー
ゴム脚・グローメット
周辺機器(C)
充電器用金具
フリーザー金具
ラッピングシステム