





NOTE:  
 64 THR'D P.I.  
 MAJOR .1875-.0028  
 PITCH .1799-.0024  
 MINCR .1708

| JKL LAMP NUMBER | VOLTS RATED | AMPS ±10% | MSCP ±25% | LUMENS ±25% | AVERAGE LIFE HRS. | FILAMENT TYPE |
|-----------------|-------------|-----------|-----------|-------------|-------------------|---------------|
| 329             | 2.5         | .400      | .500      | 6.91        | 30                | C-2R          |
| 325             | 3.0         | .190      | .250      | 3.14        | 350               | C-2R          |
| 8662            | 6.0         | .040      | .030      | 0.38        | 1,000             | C-2R          |
| 8552            | 6.3         | .200      | .550      | 6.91        | 5,000             | C-2F          |
| 8635            | 28.0        | .040      | .340      | 4.27        | 2,800             | C-2R          |

|                                                                      |  |  |                                                                                                                                |  |                                                                                                                       |  |                                                   |  |                                        |  |                                               |  |
|----------------------------------------------------------------------|--|--|--------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------|--|----------------------------------------|--|-----------------------------------------------|--|
|                                                                      |  |  | <b>METRIC</b><br><br>THIRD ANGLE PROJECTION |  | DIMENSIONS ARE IN MILLIMETERS<br>TOLERANCE UNLESS OTHERWISE SPECIFIED<br>1 PL +/- 0.2<br>2 PL +/- 0.20<br>ANGLE +/- 0 |  | <b>JKL COMPONENTS CORPORATION</b>                 |  |                                        |  |                                               |  |
|                                                                      |  |  |                                                                                                                                |  |                                                                                                                       |  | TITLE<br><b>T-1 1/4 SPECIAL MIDGET SCREW BASE</b> |  |                                        |  |                                               |  |
| A CHNG. FILAMENT TYPE FOR 325 TO C-2R<br>RELEASE & CANCEL 3515, 8645 |  |  | 9/26/06<br>10/11/00                                                                                                            |  | L. WENGSTROM<br>QC                                                                                                    |  | APPV'D BY<br>DATE 9/26/06                         |  | SIZE <b>A</b><br>FSCM NO. <b>55335</b> |  | DRAWING NO. <b>SCREW BASE SPECIAL T-1 1/4</b> |  |
| REV. NO. DESCRIPTION/ECO NUMBER                                      |  |  | APPV'D DATE                                                                                                                    |  | - CAD DRAWING -<br>MANUAL REVISIONS NOT PERMITTED                                                                     |  | SCALE<br>NONE                                     |  | RELEASED DATE<br>10/11/00              |  | REVISION DATE<br>9/26/06                      |  |
|                                                                      |  |  |                                                                                                                                |  |                                                                                                                       |  |                                                   |  | REV. NO. <b>A</b>                      |  | SHEET 1 OF 1                                  |  |