



Search:

Go

Products

Catalogs

Search

Customer Support

About Cannon

Home



Plastic / Metal Coupling / Sealed

PART NUMBER: 192993-0084

Image Disclaimer:

Please use Customer Drawing for design activity: line art and other pictures are general representations of product dimensions.

[View Line Drawings](#)



[Sales Support](#)

[Ask a Specialist](#)

[Product Home](#)

[Stock Check](#)

Product Family	Trident
Product Group	Accessory, TNM
Component	Accessory
Type of Accessory	Endbell
Sealed	Yes
Shielded	Yes
Packaging	Single
Number of Positions	19
Used Connector	TNM
Shell Size	16
Housing Material and Finish	Brass/Nickel
Grounding Ring Material and Finish	Brass/Nickel
Clamp Nut Material and Finish	Brass/Nickel
Cable Grip Material	Nylon, UL 94V-0 Rated
Support Sleeve Material	Nylon, UL 94V-0 Rated
O-Ring Material	Rubber
Environmental Sealing	Up to IP67
Flammability	UL 94V-0
For more information	Contact Cannon Sales Department
Dimension A	57,40 (2.260)
Dimension B	Ø13,60 (.535)
Dimension C	Ø27,40 (1.079)
Dimension D	22,00 (.866)
Dimension E (Standard)	88,50 (3.484) max.
Dimension E (Reversed)	80,00 (3.150) max.
Nomenclature	TNA16CCSE00L
Minimum Cable Accommodation, Outer Sheath Diameter	Ø7,90 (.311)
Maximum Cable Accommodation, Outer Sheath Diameter	Ø12,60 (.496)
Footnote	Dimensions are in mm (inch). Dimensions are subject to change.

