

Miniature Fuse, 6.3 x 32 mm, Super-Time-Lag TT, NNO, 220 VAC



220 VAC · Super-Time-Lag TT



NNO

Description

- Low Breaking Capacity

References

We recommend for new applications the type 172600
Last order date: 31.12.2013


Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Rated Voltage	32 - 220 VAC
Rated current	1.6 - 30 A
Breaking Capacity	100 A
Characteristic	Super-Time-Lag TT
Mounting	Fuseholder / Clip
Admissible Ambient Air Temp.	-40 °C to 85 °C
Climatic Category	40/085/56 acc. to IEC 60068-1
Material: Tube	Glass
Unit Weight	1.5 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	TD3AG, Current, Characteristic


Dimension



Pre-Arcing Time

Rated Current In	1.1 x In min.	1.45 x In max.	2.0 x In min.	2.0 x In max.	3.0 x In min.	3.0 x In max.	5.0 x In min.	5.0 x In max.
1.6 A - 30 A	60 min	60 min	12 s	30 s	4 s	9 s	1 s	4 s

Time-Current-Curves



All Variants

Rated Current [A]	Rated Voltage [VAC]	Breaking Capacity	Voltage Drop 1.0 In typ. [mV]	Order Number
1.6	220	1)	620	● 7045.1110
2	220	1)	470	7045.1120
2.5	220	1)	470	● 7045.1130
3.15	220	1)	370	● 7045.1140
4	220	1)	290	7045.1150
8	220	1)	170	● 7045.1180
10	220	1)	180	● 7045.1190
12.5	220	1)	120	● 7045.1210
20	32	1)	80	7045.1310
25	32	1)	70	7045.1410
30	32	1)	40	7045.1420

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

1) 100 A @ 220 VAC

Packaging Unit Small Box Pack (10 pcs.)