



Select a Category

GO

STANDARD CABLE CUTTERS

[Product Index](#) > [Cable and Bolt Cutters](#) > [Cable Cutters](#) > [Standard Cable Cutters](#) > 63041

25" Standard Cable Cutter

- *Lightweight, yet efficient shear-type cable cutters.*
- *Replaceable hook-jaw blades grab and hold cable while shear-cutting action makes clean cuts.*
- *Exceptionally strong fiberglass handles with heavy vinyl grips for comfort and slip resistance.*
- *Heavy-duty pins in head serve as blade-stops.*
- *Jaws are forged tool steel with black-oxide finish for long life.*
- *Beveled tips assure positive mating, and hinge on a rugged bolt with a pin-set nut to maintain proper blade tension.*
- *Make a clean, even cut for ease in fitting lugs and terminals.*
- *Not designed for cutting steel or ACSR.*



Buy Now!

Pictured: 63041

Line Art: 63045

Cat. No.	MCM Cable-Cutting Maximum Capacity	Overall Length	Soft Cable-Cutting Maximum Capacity	Weight (lbs.)
63041	500 Copper, 750 Aluminum	25-1/2" (648)	Soft Cable: 1-3/8" (35) diameter	5.25

All dimensions are in inches and (millimeters) except where indicated.

[Download High-Resolution .jpg photo](#)

[Download High-Resolution .jpg lineart](#)

[Download High-Resolution .eps photo](#)

[Download High-Resolution .eps lineart](#)



*The downloadable files are compressed in .zip format to save on downloading times.
Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.*

⚠ WARNINGS: Always wear approved eye protection.

⚠ WARNINGS: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

⚠ WARNINGS: Do NOT use to cut steel or ACSR.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).