

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [70929-2009](#)
Status: **Active**
Overview: [LFH™](#)
Description: 1.27mm Pitch LFH™ Matrix 50 Plug Cable Kit, Subassembly, 60 Circuits, Bright Nickel (Ni) Front Shell Plating

Documents:

3D Model	Application Specification AS-70929-001 (PDF)
Drawing (PDF)	Application Specification AS-71624-001 (PDF)
Product Specification PS-70928 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	70929
Application	Wire-to-Board
Comments	I/O Plug Connector Subassembly Use Tool 622001500 for inserting sticks into subassembly 70984 Terminal Sticks Supplied Separately
Component Type	I/O Plug Connector Subassembly
Overview	LFH™
Product Name	LFH™
Type	N/A
UPC	822350303040

Physical

Boot Color	N/A
Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Gender	Plug
Lock to Mating Part	None
Material - Metal	Aluminum
Material - Plating Mating	N/A
Material - Resin	High Temperature Thermoplastic
Net Weight	4.846/g
Number of Rows	4
Orientation	Vertical
PCB Retention	N/A
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Polarized to Mating Part	Yes
Polarized to PCB	N/A
Ports	1
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-20°C to +80°C
Termination Interface: Style	N/A
Waterproof / Dustproof	No



image - Reference only

Series

EU RoHS

ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[70929Series](#)

Mates With

[70928](#) LFH™ Receptacle

Use With

[70984](#) Terminal Stick, [71245](#) ClampShell, [71628](#) Guide Pin, Guide Sleeve [71629](#) or [71771](#), [70982](#) Hex Screw Kit

Electrical

Current - Maximum per Contact
Shield Type
Shielded
Voltage - Maximum


Full Shield
Yes
40V AC (RMS)

Material Info

Reference - Drawing Numbers

Application Specification	AS-70929-001, AS-71624-001
Product Specification	PS-70928, RPS-70928-002
Sales Drawing	SDA-70929-20**

This document was generated on 11/27/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

onlinecomponents.com